



SUINT1000XLCD Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	40	60	80	100	150	200	300	400	500	600	700	800	900
SUINT1000XLCD	Included Batteries	0	171	121	93	74	61	42	31	20	15	11	8.6	6.9	5.7	4.8
SUINT1000XLCD	BP24V15RT2U	1	499	363	282	228	191	133	100	65	47	36	28	23	19	16
SUINT1000XLCD	BP24V28-2U	1	828	610	478	391	329	233	177	117	85	65	51	42	35	30
SUINT1000XLCD	BP24V70-3U	1	1,774	1,332	1,062	879	749	541	420	285	212	164	131	109	92	79
SUINT1000XLCD	BP24V70-3U	2	3,211	2,457	1,985	1,662	1,427	1,049	825	571	432	340	275	230	196	170
SUINT1000XLCD	BP24V70-3U	3	4,494	3,488	2,845	2,400	2,072	1,540	1,221	856	654	518	422	355	304	266
SUINT1000XLCD	BP24V70-3U	4	5,645	4,436	3,649	3,096	2,687	2,014	1,606	1,135	873	696	570	480	414	362
SUINT1000XLCD	BP24V70-3U	5	6,683	5,310	4,401	3,755	3,272	2,471	1,980	1,410	1,089	872	716	606	523	460
SUINT1000XLCD	BP24V70-3U	6	7,625	6,119	5,106	4,378	3,830	2,911	2,343	1,678	1,302	1,046	862	731	633	557
SUINT1000XLCD	BP24V70-3U	7	8,483	6,870	5,768	4,968	4,361	3,336	2,696	1,942	1,511	1,218	1,006	855	742	653
SUINT1000XLCD	BP24V70-3U	8	9,269	7,568	6,391	5,529	4,869	3,746	3,039	2,200	1,718	1,388	1,149	978	850	750
SUINT1000XLCD	BP24V70-3U	9	9,989	8,219	6,979	6,061	5,355	4,142	3,373	2,452	1,921	1,555	1,290	1,100	957	846
SUINT1000XLCD	BP24V70-3U	10	10,654	8,828	7,534	6,568	5,820	4,525	3,698	2,700	2,121	1,721	1,430	1,221	1,064	941

All runtime values are shown in minutes.