



SUINT1500LCD2UN Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,350
SUINT1500LCD2UN	Internal batteries	n/a	94	49	32	23	18	14	11	9.2	7.8	6.8	6.0	5.3	4.7	4.5
SUINT1500LCD2UN	BP36V15-2U	1	335	184	122	90	70	56	47	40	34	30	26	23	21	20
SUINT1500LCD2UN	BP36V27-2US	1	460	256	172	127	99	81	67	57	49	43	38	34	31	29
SUINT1500LCD2UN	BP36V27-2US	2	832	475	326	244	193	159	133	114	98	87	77	69	63	60
SUINT1500LCD2UN	BP36V27-2US	3	1,195	695	482	364	290	240	203	173	151	133	119	107	97	93
SUINT1500LCD2UN	BP36V27-2US	4	1,550	912	637	485	389	323	274	235	205	182	162	147	133	127
SUINT1500LCD2UN	BP36V27-2US	5	1,895	1,126	792	606	488	406	345	297	260	231	207	187	170	163
SUINT1500LCD2UN	BP36V27-2US	6	2,231	1,337	945	726	586	489	417	360	316	281	252	228	208	199
SUINT1500LCD2UN	BP36V27-2US	7	2,559	1,545	1,097	845	684	572	489	423	372	331	297	270	246	236
SUINT1500LCD2UN	BP36V27-2US	8	2,878	1,750	1,247	964	782	655	561	486	428	381	343	311	285	273
SUINT1500LCD2UN	BP36V27-2US	9	3,189	1,951	1,396	1,081	879	738	633	549	484	431	389	353	323	310
SUINT1500LCD2UN	BP36V27-2US	10	3,491	2,149	1,543	1,198	975	820	704	612	540	482	435	395	362	347
SUINT1500LCD2UN	BP36V42-3U	1	881	505	347	260	206	169	142	121	105	93	82	74	67	64
SUINT1500LCD2UN	BP36V42-3U	2	1,643	969	679	518	415	345	293	252	220	195	174	157	143	137
SUINT1500LCD2UN	BP36V42-3U	3	2,363	1,421	1,006	774	625	522	446	385	338	301	270	245	223	214
SUINT1500LCD2UN	BP36V42-3U	4	3,045	1,857	1,327	1,027	834	699	599	520	458	408	367	334	305	292
SUINT1500LCD2UN	BP36V42-3U	5	3,689	2,280	1,640	1,275	1,039	875	752	653	577	515	465	423	388	372
SUINT1500LCD2UN	BP36V42-3U	6	4,300	2,688	1,946	1,519	1,242	1,048	903	786	696	623	563	513	470	451
SUINT1500LCD2UN	BP36V42-3U	7	4,879	3,084	2,245	1,759	1,442	1,220	1,052	918	814	729	660	602	553	531
SUINT1500LCD2UN	BP36V42-3U	8	5,430	3,466	2,536	1,994	1,639	1,389	1,200	1,049	931	835	757	691	635	610
SUINT1500LCD2UN	BP36V42-3U	9	5,954	3,837	2,821	2,225	1,833	1,556	1,347	1,179	1,047	941	853	780	717	689
SUINT1500LCD2UN	BP36V42-3U	10	6,453	4,196	3,100	2,452	2,025	1,722	1,492	1,308	1,163	1,045	949	868	799	768

All runtime values are shown in minutes.