



SUINT2000XLCD Estimated Runtime

UPS	External Battery Pack	BP QTY	LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,200	1,400	1,600	1,800
SUINT2000XLCD	Internal batteries	n/a	103	59	40	30	24	19	16	14	12	10	8.2	6.7	5.5	4.7
SUINT2000XLCD	BP48V27-2US	1	499	303	213	161	129	106	90	77	67	59	47	39	33	28
SUINT2000XLCD	BP48V27-2US	2	899	559	399	307	247	206	175	152	133	118	94	78	66	57
SUINT2000XLCD	BP48V27-2US	3	1,289	813	587	455	369	309	264	230	203	180	145	121	103	89
SUINT2000XLCD	BP48V27-2US	4	1,669	1,064	773	603	491	413	354	309	274	243	197	165	141	122
SUINT2000XLCD	BP48V27-2US	5	2,038	1,310	957	750	613	517	445	390	346	307	250	210	180	156
SUINT2000XLCD	BP48V27-2US	6	2,396	1,552	1,139	895	735	620	536	470	418	372	304	255	219	191
SUINT2000XLCD	BP48V27-2US	7	2,744	1,789	1,319	1,040	855	724	626	550	490	437	358	301	259	227
SUINT2000XLCD	BP48V27-2US	8	3,083	2,022	1,497	1,183	975	827	716	630	562	502	412	347	299	262
SUINT2000XLCD	BP48V27-2US	9	3,412	2,251	1,672	1,325	1,094	929	806	710	633	566	466	394	340	298
SUINT2000XLCD	BP48V27-2US	10	3,733	2,476	1,845	1,465	1,211	1,030	895	789	705	631	520	440	380	334
SUINT2000XLCD	BP48V60RT-3U	1	740	457	324	248	199	165	140	121	106	94	75	62	52	45
SUINT2000XLCD	BP48V60RT-3U	2	1,366	864	624	485	393	329	282	246	217	192	155	129	110	95
SUINT2000XLCD	BP48V60RT-3U	3	1,965	1,261	921	720	589	496	427	374	331	294	240	201	172	149
SUINT2000XLCD	BP48V60RT-3U	4	2,537	1,647	1,212	953	783	662	572	502	446	398	325	274	235	205
SUINT2000XLCD	BP48V60RT-3U	5	3,083	2,022	1,497	1,183	975	827	716	630	562	502	412	347	299	262
SUINT2000XLCD	BP48V60RT-3U	6	3,606	2,387	1,776	1,409	1,164	990	859	757	676	605	498	421	364	319
SUINT2000XLCD	BP48V60RT-3U	7	4,106	2,741	2,049	1,631	1,351	1,151	1,001	884	790	708	584	496	429	377
SUINT2000XLCD	BP48V60RT-3U	8	4,585	3,085	2,316	1,850	1,536	1,311	1,142	1,010	904	811	670	570	494	434
SUINT2000XLCD	BP48V60RT-3U	9	5,045	3,419	2,578	2,064	1,718	1,469	1,281	1,134	1,016	913	756	643	558	492
SUINT2000XLCD	BP48V60RT-3U	10	5,486	3,744	2,835	2,276	1,897	1,625	1,418	1,257	1,128	1,014	841	717	623	550

All runtime values are shown in minutes.