



SUINT2200LCD2U Estimated Runtime

| UPS | External Battery Pack | BP QTY | CONNECTED EQUIPMENT LOAD IN WATTS | | | | | | | | | | | | | |
|----------------|-----------------------|--------|-----------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | 100 | 200 | 300 | 400 | 500 | 600 | 700 | 800 | 1,000 | 1,200 | 1,400 | 1,600 | 1,800 | 1,980 |
| SUINT2200LCD2U | Internal batteries | n/a | 132 | 70 | 46 | 33 | 26 | 21 | 18 | 15 | 12 | 9.0 | 7.2 | 5.9 | 4.9 | 4.3 |
| SUINT2200LCD2U | BP48V24-2U | 1 | 457 | 254 | 170 | 126 | 98 | 80 | 67 | 57 | 44 | 35 | 29 | 24 | 21 | 18 |
| SUINT2200LCD2U | BP48V27-2US | 1 | 622 | 350 | 238 | 177 | 139 | 114 | 95 | 82 | 63 | 50 | 41 | 35 | 30 | 27 |
| SUINT2200LCD2U | BP48V27-2US | 2 | 1,108 | 641 | 443 | 335 | 266 | 220 | 186 | 160 | 124 | 100 | 83 | 71 | 61 | 54 |
| SUINT2200LCD2U | BP48V27-2US | 3 | 1,579 | 929 | 650 | 495 | 396 | 329 | 280 | 242 | 190 | 154 | 128 | 110 | 95 | 85 |
| SUINT2200LCD2U | BP48V27-2US | 4 | 2,033 | 1,212 | 854 | 654 | 527 | 439 | 375 | 326 | 256 | 209 | 175 | 150 | 131 | 117 |
| SUINT2200LCD2U | BP48V27-2US | 5 | 2,472 | 1,489 | 1,056 | 812 | 657 | 549 | 470 | 410 | 324 | 265 | 223 | 191 | 167 | 150 |
| SUINT2200LCD2U | BP48V27-2US | 6 | 2,896 | 1,760 | 1,255 | 969 | 786 | 659 | 565 | 494 | 392 | 321 | 271 | 233 | 204 | 183 |
| SUINT2200LCD2U | BP48V27-2US | 7 | 3,305 | 2,026 | 1,451 | 1,125 | 915 | 768 | 660 | 578 | 460 | 378 | 320 | 276 | 242 | 217 |
| SUINT2200LCD2U | BP48V27-2US | 8 | 3,701 | 2,286 | 1,644 | 1,278 | 1,042 | 877 | 755 | 661 | 528 | 435 | 368 | 318 | 279 | 251 |
| SUINT2200LCD2U | BP48V27-2US | 9 | 4,084 | 2,541 | 1,835 | 1,430 | 1,168 | 985 | 849 | 745 | 595 | 492 | 417 | 361 | 317 | 286 |
| SUINT2200LCD2U | BP48V27-2US | 10 | 4,454 | 2,791 | 2,023 | 1,580 | 1,293 | 1,092 | 942 | 828 | 663 | 549 | 466 | 404 | 355 | 320 |
| SUINT2200LCD2U | BP48V60RT-3U | 1 | 915 | 525 | 361 | 271 | 215 | 177 | 149 | 128 | 99 | 80 | 66 | 56 | 48 | 43 |
| SUINT2200LCD2U | BP48V60RT-3U | 2 | 1,671 | 986 | 691 | 527 | 423 | 351 | 299 | 259 | 203 | 165 | 138 | 118 | 102 | 91 |
| SUINT2200LCD2U | BP48V60RT-3U | 3 | 2,386 | 1,434 | 1,016 | 781 | 631 | 527 | 451 | 393 | 310 | 254 | 213 | 183 | 160 | 143 |
| SUINT2200LCD2U | BP48V60RT-3U | 4 | 3,061 | 1,867 | 1,334 | 1,032 | 838 | 703 | 603 | 527 | 419 | 344 | 291 | 250 | 219 | 197 |
| SUINT2200LCD2U | BP48V60RT-3U | 5 | 3,701 | 2,286 | 1,644 | 1,278 | 1,042 | 877 | 755 | 661 | 528 | 435 | 368 | 318 | 279 | 251 |
| SUINT2200LCD2U | BP48V60RT-3U | 6 | 4,307 | 2,691 | 1,948 | 1,520 | 1,243 | 1,049 | 905 | 795 | 636 | 526 | 447 | 387 | 340 | 306 |
| SUINT2200LCD2U | BP48V60RT-3U | 7 | 4,883 | 3,084 | 2,244 | 1,758 | 1,442 | 1,219 | 1,054 | 927 | 744 | 617 | 525 | 455 | 401 | 362 |
| SUINT2200LCD2U | BP48V60RT-3U | 8 | 5,430 | 3,464 | 2,534 | 1,992 | 1,637 | 1,387 | 1,201 | 1,058 | 851 | 707 | 603 | 524 | 462 | 417 |
| SUINT2200LCD2U | BP48V60RT-3U | 9 | 5,950 | 3,832 | 2,817 | 2,221 | 1,830 | 1,553 | 1,347 | 1,188 | 957 | 797 | 680 | 592 | 523 | 473 |
| SUINT2200LCD2U | BP48V60RT-3U | 10 | 6,446 | 4,189 | 3,093 | 2,447 | 2,020 | 1,717 | 1,491 | 1,316 | 1,063 | 886 | 758 | 660 | 584 | 528 |

All runtime values are shown in minutes.