



SUINT3000LCD2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,300	1,500	1,700	2,000	2,200	2,500	2,700
SUINT3000LCD2U	Internal batteries	0	196	107	72	53	34	24	19	14	12	9.8	7.8	6.8	5.6	5.0
SUINT3000LCD2U	BP72V15-2U	1	560	318	217	161	104	75	57	42	35	30	24	21	18	16
SUINT3000LCD2U	BP72V18-2US	1	652	373	255	191	123	89	68	50	42	36	29	25	22	19
SUINT3000LCD2U	BP72V18-2US	2	1,104	647	450	341	225	164	128	94	79	68	55	49	42	38
SUINT3000LCD2U	BP72V18-2US	3	1,542	918	645	493	329	243	190	141	119	103	84	75	64	58
SUINT3000LCD2U	BP72V18-2US	4	1,967	1,184	839	644	433	322	254	190	161	139	114	102	87	79
SUINT3000LCD2U	BP72V18-2US	5	2,377	1,446	1,030	794	538	402	318	239	203	176	145	130	111	101
SUINT3000LCD2U	BP72V18-2US	6	2,775	1,702	1,218	943	643	482	383	289	246	213	177	158	136	124
SUINT3000LCD2U	BP72V18-2US	7	3,160	1,954	1,405	1,091	747	562	448	339	290	251	209	187	161	147
SUINT3000LCD2U	BP72V18-2US	8	3,533	2,200	1,588	1,237	850	642	513	390	333	290	241	216	186	170
SUINT3000LCD2U	BP72V18-2US	9	3,894	2,442	1,769	1,382	953	722	577	440	377	328	273	245	212	194
SUINT3000LCD2U	BP72V18-2US	10	4,244	2,679	1,948	1,525	1,055	801	642	491	421	367	306	275	238	218
SUINT3000LCD2U	BP72V28RT3U	1	925	538	372	280	184	134	104	76	64	55	44	39	33	30
SUINT3000LCD2U	BP72V28RT3U	2	1,628	972	684	523	350	258	203	151	128	110	90	80	68	62
SUINT3000LCD2U	BP72V28RT3U	3	2,296	1,394	992	764	517	386	305	229	195	168	139	124	106	97
SUINT3000LCD2U	BP72V28RT3U	4	2,930	1,803	1,293	1,003	684	514	409	309	264	229	189	170	146	133
SUINT3000LCD2U	BP72V28RT3U	5	3,533	2,200	1,588	1,237	850	642	513	390	333	290	241	216	186	170
SUINT3000LCD2U	BP72V28RT3U	6	4,106	2,585	1,877	1,468	1,014	769	616	470	403	351	293	263	227	208
SUINT3000LCD2U	BP72V28RT3U	7	4,651	2,958	2,159	1,695	1,177	895	719	551	473	413	345	310	269	246
SUINT3000LCD2U	BP72V28RT3U	8	5,171	3,319	2,435	1,917	1,337	1,021	821	631	543	475	398	358	311	285
SUINT3000LCD2U	BP72V28RT3U	9	5,668	3,671	2,705	2,136	1,496	1,145	923	711	613	536	450	406	352	324
SUINT3000LCD2U	BP72V28RT3U	10	6,142	4,011	2,969	2,352	1,653	1,268	1,025	791	682	598	503	453	394	362

All runtime values are shown in minutes.