



SUINT3000LCD2UN Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	300	500	700	900	1,100	1,300	1,500	1,700	1,900	2,100	2,300	2,500	2,700
SUINT3000LCD2UN	Internal batteries	n/a	196	72	41	28	21	17	14	12	9.8	8.4	7.3	6.4	5.6	5.0
SUINT3000LCD2UN	BP72V15-2U	1	560	217	127	87	65	51	42	35	30	26	22	20	18	16
SUINT3000LCD2UN	BP72V18-2US	1	652	255	151	104	78	61	50	42	36	31	27	24	22	19
SUINT3000LCD2UN	BP72V18-2US	2	1,104	450	272	190	144	115	94	79	68	59	52	46	42	38
SUINT3000LCD2UN	BP72V18-2US	3	1,542	645	396	280	213	171	141	119	103	90	79	71	64	58
SUINT3000LCD2UN	BP72V18-2US	4	1,967	839	520	370	284	229	190	161	139	121	108	96	87	79
SUINT3000LCD2UN	BP72V18-2US	5	2,377	1,030	643	461	356	287	239	203	176	154	137	123	111	101
SUINT3000LCD2UN	BP72V18-2US	6	2,775	1,218	766	552	427	346	289	246	213	188	167	150	136	124
SUINT3000LCD2UN	BP72V18-2US	7	3,160	1,405	888	642	499	405	339	290	251	221	197	177	161	147
SUINT3000LCD2UN	BP72V18-2US	8	3,533	1,588	1,010	733	571	464	390	333	290	255	228	205	186	170
SUINT3000LCD2UN	BP72V18-2US	9	3,894	1,769	1,130	822	642	524	440	377	328	290	259	233	212	194
SUINT3000LCD2UN	BP72V18-2US	10	4,244	1,948	1,249	912	713	583	491	421	367	324	290	261	238	218
SUINT3000LCD2UN	BP72V28-3U	1	925	372	223	155	117	93	76	64	55	47	42	37	33	30
SUINT3000LCD2UN	BP72V28-3U	2	1,628	684	420	298	228	182	151	128	110	96	85	76	68	62
SUINT3000LCD2UN	BP72V28-3U	3	2,296	992	619	443	341	275	229	195	168	148	131	118	106	97
SUINT3000LCD2UN	BP72V28-3U	4	2,930	1,293	815	588	456	370	309	264	229	201	179	161	146	133
SUINT3000LCD2UN	BP72V28-3U	5	3,533	1,588	1,010	733	571	464	390	333	290	255	228	205	186	170
SUINT3000LCD2UN	BP72V28-3U	6	4,106	1,877	1,202	876	685	559	470	403	351	310	277	250	227	208
SUINT3000LCD2UN	BP72V28-3U	7	4,651	2,159	1,391	1,018	798	653	551	473	413	365	327	295	269	246
SUINT3000LCD2UN	BP72V28-3U	8	5,171	2,435	1,577	1,159	911	747	631	543	475	421	377	341	311	285
SUINT3000LCD2UN	BP72V28-3U	9	5,668	2,705	1,762	1,298	1,023	841	711	613	536	476	427	386	352	324
SUINT3000LCD2UN	BP72V28-3U	10	6,142	2,969	1,943	1,436	1,134	934	791	682	598	531	477	432	394	362

All runtime values are shown in minutes.