



## SUINT3000RTXL2U Estimated Runtime

UPS		Load in Watts													
		100	200	300	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,500
SUINT3000RTXL2U	Internal batteries	126	81	58	45	31	23	19	16	13	11	9.5	8.2	7.2	6.0

Maximum load 2500 watts without external battery packs. All runtime values are shown in minutes.

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400
SUINT3000RTXL2U	BP72V15-2U	1	372	241	175	136	91	67	53	43	36	31	27	24	21	19
SUINT3000RTXL2U	BP72V18-2US	1	435	284	207	161	109	80	63	51	43	37	33	29	26	23
SUINT3000RTXL2U	BP72V18-2US	2	749	499	369	290	199	149	118	96	82	71	62	55	50	45
SUINT3000RTXL2U	BP72V18-2US	3	1,058	713	532	421	292	221	175	144	123	107	94	84	76	69
SUINT3000RTXL2U	BP72V18-2US	4	1,361	924	694	552	386	293	234	194	166	145	128	114	103	94
SUINT3000RTXL2U	BP72V18-2US	5	1,657	1,133	855	682	481	367	294	244	210	183	162	145	131	120
SUINT3000RTXL2U	BP72V18-2US	6	1,947	1,339	1,014	812	575	441	355	295	254	222	197	177	160	146
SUINT3000RTXL2U	BP72V18-2US	7	2,230	1,542	1,172	941	669	514	415	346	298	262	233	209	189	173
SUINT3000RTXL2U	BP72V18-2US	8	2,507	1,741	1,327	1,068	762	588	476	397	343	302	269	241	219	200
SUINT3000RTXL2U	BP72V18-2US	9	2,778	1,938	1,482	1,195	855	661	536	449	388	341	304	274	249	227
SUINT3000RTXL2U	BP72V18-2US	10	3,043	2,132	1,634	1,320	948	734	596	500	433	381	340	307	278	255
SUINT3000RTXL2U	BP72V28RT3U	1	624	413	304	238	162	121	95	78	66	57	50	45	40	36
SUINT3000RTXL2U	BP72V28RT3U	2	1,119	755	564	447	311	235	187	154	132	115	101	90	81	74
SUINT3000RTXL2U	BP72V28RT3U	3	1,598	1,092	823	656	462	352	282	234	201	176	156	139	126	114
SUINT3000RTXL2U	BP72V28RT3U	4	2,061	1,420	1,077	864	613	470	379	315	271	238	212	190	172	157
SUINT3000RTXL2U	BP72V28RT3U	5	2,507	1,741	1,327	1,068	762	588	476	397	343	302	269	241	219	200
SUINT3000RTXL2U	BP72V28RT3U	6	2,937	2,054	1,573	1,270	911	705	572	479	415	365	326	294	267	244
SUINT3000RTXL2U	BP72V28RT3U	7	3,353	2,360	1,814	1,469	1,058	822	669	561	486	429	384	346	314	288
SUINT3000RTXL2U	BP72V28RT3U	8	3,755	2,658	2,051	1,666	1,204	938	764	643	558	493	441	398	363	332
SUINT3000RTXL2U	BP72V28RT3U	9	4,143	2,950	2,284	1,859	1,348	1,053	860	724	630	557	499	451	411	377
SUINT3000RTXL2U	BP72V28RT3U	10	4,518	3,234	2,512	2,049	1,491	1,167	955	806	701	621	557	504	459	421

Maximum load 2400 watts with external battery packs. All runtime values are shown in minutes.