



SUINT3000XLCD Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	300	500	700	900	1,100	1,300	1,500	1,700	1,900	2,100	2,300	2,500	2,700
SUINT3000XLCD	Internal batteries	n/a	169	65	38	25	19	15	12	10	8.3	7.1	6.2	5.5	4.9	4.4
SUINT3000XLCD	BP72V15-2U	1	495	206	124	86	64	51	42	35	30	26	23	20	18	16
SUINT3000XLCD	BP72V18-2US	1	577	243	147	102	77	61	50	42	36	31	27	24	22	20
SUINT3000XLCD	BP72V18-2US	2	982	430	265	188	143	114	94	79	68	59	52	47	42	38
SUINT3000XLCD	BP72V18-2US	3	1,377	617	386	276	212	170	141	120	103	90	80	71	64	59
SUINT3000XLCD	BP72V18-2US	4	1,760	802	507	365	282	228	190	161	139	122	108	97	88	80
SUINT3000XLCD	BP72V18-2US	5	2,133	986	628	455	353	286	239	204	176	155	138	124	112	102
SUINT3000XLCD	BP72V18-2US	6	2,495	1,167	749	545	424	345	289	247	214	189	168	151	137	125
SUINT3000XLCD	BP72V18-2US	7	2,846	1,347	868	634	495	404	339	290	252	223	199	179	162	148
SUINT3000XLCD	BP72V18-2US	8	3,188	1,523	987	723	566	463	390	334	291	257	229	207	188	172
SUINT3000XLCD	BP72V18-2US	9	3,520	1,698	1,105	812	637	522	440	378	329	291	260	235	214	196
SUINT3000XLCD	BP72V18-2US	10	3,843	1,870	1,222	900	708	581	490	421	368	326	292	263	240	220
SUINT3000XLCD	BP72V28RT-3U	1	821	355	217	153	116	92	76	64	55	48	42	37	34	31
SUINT3000XLCD	BP72V28RT-3U	2	1,455	654	410	294	226	182	151	128	110	96	85	76	69	63
SUINT3000XLCD	BP72V28RT-3U	3	2,059	949	604	437	339	274	229	195	169	148	132	118	107	98
SUINT3000XLCD	BP72V28RT-3U	4	2,637	1,239	797	580	453	369	309	264	229	202	180	162	147	134
SUINT3000XLCD	BP72V28RT-3U	5	3,188	1,523	987	723	566	463	390	334	291	257	229	207	188	172
SUINT3000XLCD	BP72V28RT-3U	6	3,715	1,801	1,175	865	680	557	470	404	353	312	279	252	229	210
SUINT3000XLCD	BP72V28RT-3U	7	4,219	2,074	1,361	1,005	793	651	551	474	414	367	329	298	271	249
SUINT3000XLCD	BP72V28RT-3U	8	4,702	2,340	1,544	1,144	905	745	631	544	476	423	379	343	313	288
SUINT3000XLCD	BP72V28RT-3U	9	5,164	2,601	1,724	1,282	1,016	838	711	614	538	478	430	389	355	327
SUINT3000XLCD	BP72V28RT-3U	10	5,608	2,856	1,902	1,418	1,126	931	791	684	600	534	480	435	398	366

All runtime values are shown in minutes.