



## SUTX20K Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2kW	4kW	6kW	8kW	10kW	12kW	13kW	14kW	15kW	16kW	17kW	18kW	19kW	20kW
SUTX20K	INCLUDED BATTERIES	0	189	91	58	43	33.4	27	24	22	20	19	18	16	15	14.3
SUTX20K	BP480V26B	1	467	224	141	101	78	62	56	51	47	43	40	37	35	33
SUTX20K	BP480V26B	2	782	387	248	180	139	112	101	93	85	79	73	68	63	60
SUTX20K	BP480V40C	1	637	311	198	142	110	88	80	73	67	62	57	53	50	47
SUTX20K	BP480V40C	2	1,119	566	369	269	210	170	154	141	130	120	112	104	98	92
SUTX20K	BP480V200	1	819	406	261	189	146	118	107	98	90	83	77	72	67	63
SUTX20K	BP480V200	2	1,471	758	500	368	288	234	214	196	181	168	156	146	137	129
SUTX20K	BP480V200	3	2,095	1,106	739	549	433	355	325	299	277	257	240	225	211	199
SUTX20K	BP480V200	4	2,690	1,445	976	730	580	477	438	404	375	349	326	306	288	272
SUTX20K	BP480V300	1	1,095	553	360	263	204	165	150	138	127	117	109	102	95	89
SUTX20K	BP480V300	2	1,995	1,050	700	519	410	335	307	282	261	243	226	212	199	188
SUTX20K	BP480V300	3	2,837	1,531	1,035	776	617	508	467	431	400	372	348	327	308	291
SUTX20K	BP480V300	4	3,624	1,995	1,364	1,029	822	681	627	580	539	503	471	443	418	395
SUTX20K	BP480V400	1	1,390	714	469	345	269	219	200	183	169	157	146	136	128	120
SUTX20K	BP480V400	2	2,541	1,360	916	684	542	446	409	377	350	325	304	285	268	253
SUTX20K	BP480V400	3	3,595	1,977	1,351	1,020	815	675	621	574	533	498	466	438	413	391
SUTX20K	BP480V400	4	4,563	2,567	1,773	1,348	1,083	901	830	770	716	670	629	592	559	529
SUTX20K	BP480V500	1	1,815	949	631	467	367	300	274	252	233	216	202	189	177	167
SUTX20K	BP480V500	2	3,308	1,806	1,230	926	738	611	561	519	482	449	421	395	373	352
SUTX20K	BP480V500	3	4,634	2,611	1,805	1,373	1,103	919	847	785	731	683	641	604	570	540
SUTX20K	BP480V500	4	5,821	3,367	2,356	1,806	1,459	1,221	1,127	1,047	977	915	860	811	767	727

All runtime values are shown in minutes.