



SV40KM2POB Estimated Runtime

Modular UPS Configuration	Battery Model	Battery Qty.	Load in Kilowatts (kW)														
			8kW	10kW	12kW	14kW	16kW	18kW	20kW	22kW	24kW	26kW	28kW	30kW	32kW	34kW	36kW
<i>*External Battery Packs</i>																	
SV40KM2POB	EBP240V2501	1	72	55	44	36	31	27	23	20	18	16	15	14	12	11	10.5
SV40KM2POB	EBP240V3501	1	97	75	60	50	42	37	32	28	25	23	21	19	17	16	15
SV40KM2POB	EBP240V5001	1	143	111	89	74	63	55	48	43	38	34	31	29	26	24	23
SV40KM2POB	EBP240V2502	1	165	129	104	87	74	64	56	50	45	40	37	34	31	29	27
SV40KM2POB	EBP240V3502	1	221	173	141	118	101	88	77	68	61	55	51	46	43	39	37
SV40KM2POB	EBP240V5002	1	317	250	204	172	147	129	113	101	91	82	75	69	64	59	55
SV40KM2POB	EBP240V6002	1	343	270	222	186	160	140	123	110	99	90	82	75	69	64	60
SV40KM2POB	EBP240V6003	1	534	424	350	297	256	225	199	178	161	146	134	123	114	106	99
SV40KM2POB	BP240V370*	1	287	226	184	155	133	116	102	90	81	73	67	61	56	52	49
SV40KM2POB	BP240V370*	2	611	488	403	342	296	260	230	206	186	169	155	142	132	122	114
SV40KM2POB	BP240V370*	3	932	750	624	533	464	409	364	327	296	270	248	229	212	198	185

All runtime values are shown in minutes.

**Similar performance is available using BP240V370NB battery cabinet with user-supplied batteries.*