



## SV60KM3POB Estimated Runtime

Modular UPS Configuration	Battery Model	Battery Qty.	Load in Kilowatts (kW)														
			12kW	15kW	18kW	21kW	24kW	27kW	30kW	33kW	36kW	39kW	42kW	45kW	48kW	51kW	54kW
<i>External Battery Packs</i>																	
SV60KM3POB	EBP240V2501	1	44	34	27	22	19	16	14	12	11	10	8.7	7.9	7.2	6.6	6.0
SV60KM3POB	EBP240V3501	1	61	46	37	31	26	22	19	17	15	14	12	11	10	9.4	8.6
SV60KM3POB	EBP240V5001	1	90	69	56	46	39	34	29	26	23	21	19	17	16	14	13
SV60KM3POB	EBP240V2502	1	105	81	65	54	46	40	34	30	27	24	22	20	19	17	16
SV60KM3POB	EBP240V3502	1	141	110	89	74	63	54	47	42	37	34	31	28	26	24	22
SV60KM3POB	EBP240V5002	1	205	160	130	109	93	81	71	63	56	51	46	42	39	36	33
SV60KM3POB	EBP240V6002	1	222	174	141	118	101	88	77	68	61	55	50	46	42	39	36
SV60KM3POB	EBP240V6003	1	351	277	227	191	164	144	126	112	101	91	83	76	71	65	61
SV60KM3POB	BP240V370*	1	181	141	114	95	81	70	62	55	49	44	40	37	34	31	29
SV60KM3POB	BP240V370*	2	396	313	257	217	186	163	144	128	115	104	95	87	81	75	70
SV60KM3POB	BP240V370*	3	613	488	404	343	297	260	230	206	186	169	155	142	132	122	114

*All runtime values are shown in minutes.*

*\*Similar performance is available using BP240V370NB battery cabinet with user-supplied batteries.*