



SV60KS3POB Estimated Runtime

Modular UPS Configuration	Battery Model	Battery Qty.	Load in Kilowatts (kW)														
			12kW	15kW	18kW	21kW	24kW	27kW	30kW	33kW	36kW	39kW	42kW	45kW	48kW	51kW	54kW
<i>External Battery Packs</i>																	
SV60KS3POB	EBP240V2501	1	43	33	26	22	18	16	14	12	11	9.4	8.5	7.7	7.0	6.5	5.9
SV60KS3POB	EBP240V3501	1	59	45	36	30	25	22	19	17	15	13	12	11	10.0	9.2	8.5
SV60KS3POB	EBP240V5001	1	87	67	54	45	38	33	29	25	23	20	18	17	15	14	13
SV60KS3POB	EBP240V2502	1	102	79	63	52	45	38	34	30	27	24	22	20	18	17	16
SV60KS3POB	EBP240V3502	1	138	107	86	72	61	53	46	41	37	33	30	28	25	23	22
SV60KS3POB	EBP240V5002	1	200	156	127	106	90	79	69	61	55	50	45	41	38	35	33
SV60KS3POB	EBP240V6002	1	217	170	138	115	99	86	75	67	60	54	49	45	42	39	36
SV60KS3POB	EBP240V6003	1	343	271	222	187	160	140	123	110	99	90	82	75	69	64	60
SV60KS3POB	BP240V370*	1	176	137	111	93	79	69	60	53	48	43	39	36	33	31	28
SV60KS3POB	BP240V370*	2	387	306	251	211	182	159	140	125	113	102	94	86	79	74	69
SV60KS3POB	BP240V370*	3	599	477	394	335	289	254	225	202	183	166	152	140	130	121	113

All runtime values are shown in minutes.

*Similar performance is available using BP240V370NB battery cabinet with user-supplied batteries.