

Eaton 9PX UPS bundles

Configuration overview

Delivering premium backup power and scalable battery runtimes for servers, voice/data networks and storage systems, the Eaton® 9PX UPS is the ideal solution for both rack and stand-alone installations.



5 and 6 kVA 208V output

| Catalog number | Bundle contents | Description | Power rating (VA/watts) | Input plug | Output receptacles | Rack height |
|----------------|-----------------|------------------|-------------------------|---------------------------------|------------------------------------|-------------|
| 9PX5K | 9PX5K | 5 kVA UPS | 5000/4500 | Terminal block with L6-30P cord | Hardwired + (2) L6-30R, (2) L6-20R | 3U |
| 9PX6K | 9PX6K | 6 kVA UPS | 6000/5400 | Terminal block with L6-30P cord | Hardwired + (2) L6-30R, (2) L6-20R | 3U |
| 9PX6KG | 9PX6KG | 6 kVA UPS Global | 6000/5400 | Hardwired | Hardwired + (2) C19, (8) C13 | 3U |



5 and 6 kVA 120/208V output

| Catalog number | Bundle contents | Description | Power rating (VA/watts) | Input plug | Output receptacles | Rack height |
|----------------|-------------------|--------------------------------|-------------------------|---------------------------------|--|-------------|
| 9PX5KTF5 | 9PX5K 9PXTFMR5 | 5 kVA UPS 5 kVA Transformer | 5000/4500 | Terminal block with L6-30P cord | Hardwired + (1) L6-30R, (2) L6-20R, (18) 5-20R | 6U |
| 9PX6KTF5 | 9PX6K 9PXTFMR5 | 6 kVA UPS 5 kVA Transformer | 6000/5400 | Terminal block with L6-30P cord | Hardwired + (1) L6-30R, (2) L6-20R, (18) 5-20R | 6U |



5 and 6 kVA 120/208V output with maintenance bypass

| Catalog number | Bundle contents | Description | Power rating (VA/watts) | Input plug | Output receptacles | Rack height |
|----------------|-------------------|---|-------------------------|------------|--|-------------|
| 9PX5KP1 | 9PX5K 9PXPPDM1 | 5 kVA UPS 6 kVA PPDM (plug and play model for rackmount applications) | 5000/4500 | L6-30P | (1) L14-30R, (1) L6-30R, (6) 5-20R | 6U |
| 9PX5KP2 | 9PX5K 9PXPPDM2 | 5 kVA UPS 6 kVA PPDM (hardwired model for installations using conduit) | 5000/4500 | Hardwired | Hardwired | 6U |
| 9PX6KP1 | 9PX6K 9PXPPDM1 | 6 kVA UPS 6 kVA PPDM (plug and play model for rackmount applications) | 6000/5400 | L6-30P | (1) L14-30R, (1) L6-30R, (6) 5-20R | 6U |
| 9PX6KP2 | 9PX6K 9PXPPDM2 | 6 kVA UPS 6 kVA PPDM (hardwired model for installations using conduit) | 6000/5400 | Hardwired | Hardwired | 6U |

PPDM—PowerPass distribution module allows a step-down voltage to 120V to accommodate a variety of IT equipment. The PPDM also provides a maintenance bypass, which allows you to service or replace the entire UPS without powering down IT equipment.

Transformer—Provides 120/240V output through receptacles and/or hardwired output.



Visit Eaton.com/9PX to interact with these 9PX models.



Powering Business Worldwide



8 and 11 kVA 208V output

| Catalog number | Bundle contents | Description | Power rating (VA/watts) | Input plug | Output receptacles | Rack height |
|----------------|--------------------------------------|---|-------------------------|------------|------------------------|-------------|
| 9PX8KHW | 9PX8KPM 9PXEBM240RT | 8 kVA Power module 11 kVA EBM | 8000/7200 | Hardwired | Hardwired | 6U |
| 9PX11KHW | 9PX11KPM 9PXEBM240RT | 11 kVA Power module 11 kVA EBM | 11000/10000 | Hardwired | Hardwired | 6U |
| 9PX8K | 9PX8KPM 9PXEBM240RT MBP11K208 | 8 kVA Power module 11 kVA EBM 11 kVA MBP | 8000/7200 | Hardwired | Hardwired + (3) L6-30R | 6U |
| 9PX11K | 9PX11KPM 9PXEBM240RT MBP11K208 | 11 kVA Power module 11 kVA EBM 11 kVA MBP | 11000/10000 | Hardwired | Hardwired + (3) L6-30R | 6U |



8 and 11 kVA 120/208V output

| Catalog number | Bundle contents | Description | Power rating (VA/watts) | Input plug | Output receptacles | Rack height |
|----------------|--|--|-------------------------|------------|------------------------------------|-------------|
| 9PX8KTF5 | 9PX8KPM 9PXEBM240RT MBP11K208 9PXTFMR5 | 8 kVA Power module 11 kVA EBM 11 kVA MBP 5 kVA Transformer | 8000/7200 | Hardwired | (2) L6-30R, (18) 5-20R | 9U |
| 9PX11KTF5 | 9PX11KPM 9PXEBM240RT MBP11K208 9PXTFMR5 | 11 kVA Power module 11 kVA EBM 11 kVA MBP 5 kVA Transformer | 11000/10000 | Hardwired | (2) L6-30R, (18) 5-20R | 9U |
| 9PX11KTF11 | 9PX11KPM 9PXEBM240RT 9PXTFMR11 | 11 kVA Power module 11 kVA EBM 11 kVA Transformer | 11000/10000 | Hardwired | Hardwired + (2) L14-30R, (8) 5-20R | 9U |

Power module—The 8 and 11 kVA 9PX UPSs are composed of one power module (electronics only) and one external battery module (EBM).

MBP—Maintenance bypass switch allows for easy transition between UPS mode and bypass mode in order to perform maintenance. MBP also provides (3) L6-30R output receptacles.



Visit Eaton.com/9PX to interact with these 9PX models.