

Power and charge electronics in professional environments



Designed to unite form and function, Safe-IT surge protectors and power strips are suitable for powering and charging electronics in professional environments.

Perfect for:

Offices, lobbies, conference rooms and other shared spaces where appearances matter.

Safe-IT professional-grade surge protectors and power strips combine a stylish design with convenient access to power and charging for electronic devices. The surge protectors safeguard devices connected to AC outlets from the damaging effects of power surges, spikes and line noise.

As part of the Safe-IT family of products, these power solutions have antimicrobial properties to help resist the growth of bacteria, viruses, fungi, mold and mildew. They can help provide peace of mind in environments where multiple users frequently plug in devices.

Key benefits

STYLISH DESIGN

- These surge protectors and power strips are designed to be appropriate for any space, from home offices to high-end hotel lobbies.

RELIABLE POWER DISTRIBUTION

- NEMA 5-15R outlets distribute power to as many as six devices using only one AC wall outlet.
- Surge-protected AC outlets safeguard devices from the damaging effects of power surges, spikes and line noise.

CONVENIENT DEVICE CHARGING

- Most models feature USB charging ports to conveniently keep smartphones, tablets and other mobile devices ready for use.
- USB ports eliminate the need for an AC adapter for charging cords, leaving outlets available for AC equipment.
- Qi wireless charging options on the desktop charger, TLM210CAM, and the mobile tower, TLM610CPAM, reduce cord clutter.

DIVERSE FORM FACTORS

- In-desk models offer easy access to power and charging ports. TLP12POAM is flush with the desktop, and PS22POPAM has a pop-up design. PS222DATAM stays recessed in the desktop.
- Strip model, TLP610COILAM, has a 10 ft. power cord with a coiled design to take up less space.
- Desktop model, TLM210CAM, has outlets, charging ports and wireless charging pads on two sides, making it ideal for shared spaces.
- Mobile tower model, TLM610CPAM, has outlets, charging ports and wireless charging pockets on three sides. Use with or without the included swivel casters. Heavy-duty steel base has mounting holes and a Nano slot to accept a security lock (not included).

ANTIMICROBIAL PROTECTION

- Antimicrobial protection aids in resisting the growth of bacteria, viruses, fungi, mold and mildew.

Surge Protector Feature Focus

A Surge-Protected AC Outlet(s)



B USB-A Charging Ports



C USB-C Charging Port



D Wireless Charging Pad

E Lighted On/Off Switch

The switch confirms power status and provides one-touch control over connected equipment.



F Wireless Charging Pocket

Three pockets charge smartphones without cable clutter.

G Input Power Plug

H Cord Wrap

Power cord stays out of the way during movement.

I Swivel Casters

J Kensington NanoSaver Lock Slot


The slot accepts a compatible security lock (not included).

Antimicrobial Protection

Antimicrobial protection aids in resisting the growth of bacteria, viruses, fungi, mold and mildew.



TLP12POAM



TLP610COILAM



TLM210CAM




TLM610CPAM

Power Strip Feature Focus

- A** AC Outlets
- B** USB-A Charging Ports
- C** USB-A Hub Ports
- D** HDMI Coupler
- E** USB-B Port
- F** Phone Coupler (RJ11)
- G** Ethernet Coupler (RJ45)
- H** Input Power Plug



PS22POPAM



PS22DATAM

PS22DATAM (Bottom)

Antimicrobial Protection

Antimicrobial protection aids in resisting the growth of bacteria, viruses, fungi, mold and mildew.

SURGE PROTECTOR SPECIFICATIONS

Models	TLP12POAM	TLP610COILAM	TLM210CAM	TLM610CPAM
Form Factor	In-desk grommet for 3" dia. opening	Strip	Desktop	Mobile tower with floor-mount option
AC Outlet Qty. (Type)	1 (NEMA 5-15R)	6 (NEMA 5-15R)	2 (NEMA 5-15R)	6 (NEMA 5-15R)
Surge Protection	1000 joules	300 joules	1000 joules	1000 joules
USB-A Charging Ports	2 (4.2A total)	—	4 (2 x 2.4A, 2 x 2.1A)	4 (2 x 2.4A, 2 x 2.1A)
USB-C Charging Ports	—	—	2 x 60W	1 x 60W
Wireless Charging	—	—	2 pads x 10W	3 pockets x 3.1A
Input Plug Type	NEMA 5-15P (right angle)	NEMA 5-15P (right angle)	NEMA 5-15P (right angle)	NEMA 5-15P
Input Cord Length	10 ft.	10 ft. Coiled	10 ft. Braided	10 ft. Braided
Unit Dimensions	3.54" Dia. (top) to 2.98" Dia. (bottom) x 3.35" H	1.7" H x 9.5" W x 1.9" D	4.3" H x 14.8" W x 4.9" D	13" Dia. X 39" H
Housing Material	Plastic	Plastic	Metal	Metal
Antimicrobial Properties	Yes	Yes	Yes	Yes
Warranty	Lifetime limited	Lifetime limited	Lifetime limited	Lifetime limited
Connected Equipment Insurance	\$15,000	\$10,000	\$50,000	\$50,000

POWER STRIP SPECIFICATIONS

Models	PS22POPAM	PS22DATAM
Form Factor	In-desk pop-up for 3" dia. opening	In-desk for 7.95" x 4.06" opening
AC Outlet Qty. (Type)	2 (NEMA 5-15R)	2 (NEMA 5-15R)
USB-A Charging Ports	2 (4.5A total)	2 (4.5A total)
USB-A Data Ports	—	2
USB-B Port	—	1
HDMI Coupler	—	1
Phone Coupler	—	1 (RJ11)
Ethernet Coupler	—	1 (RJ45)
Input Plug Type	NEMA 5-15P (right angle)	NEMA 5-15P (right angle)
Input Cord Length	6 ft.	10 ft.
Unit Dimensions	2.95" Dia. (top) to 3" Dia. (bottom) x 10.14" H	8.76" W x 3.67" D
Housing Material	Plastic	Plastic
Antimicrobial Properties	Yes	Yes
Warranty	Lifetime limited	Lifetime limited

Learn more about our full line of surge protectors and power strips at tripplite.eaton.com.

TRIPP-LITE
by **EATON**