

TRIPP-LITE

Pro AV Mobile Carts

by **EATON**

Mobile TV/monitor mounts accentuate your message in upscale spaces



Pro AV mobile carts stand up to years of use, and their contemporary design is ideal for boardrooms and customer-facing areas.

Perfect for:

Contemporary corporate offices, waiting rooms, medical facilities and other places where appearances matter most.

Elevate the style of presentations on TVs and monitors with Pro AV mobile carts. With a sleek frame and glass shelves and bases, these carts add a touch of elegance to a functional design, helping them fit in with high-end office décor.

Four mobile cart models support 32 to 70 in. displays weighing up to 175 lb. Locking casters make them easy to position within a room and to relocate across a hall. They combine form and convenience to help keep your audience focused on the message.

Key benefits

CONVENIENT MOBILITY

- Casters provide smooth rolling, allowing users to take their message to their audience.
- Cart mobility allows AV resources to be shared within a facility.
- Casters lock to keep the carts stationary when desired.

CONTEMPORARY APPEARANCE

- Sleek design with black or white frosted glass shelf and base helps carts blend in with high-end furnishings.
- Carts with white glass have a white gloss finish on the frame; the all-white look can help brighten spaces.
- Included cable covers keep cables organized for a more polished appearance.



ADJUSTABLE VIEWING

- The display can be raised or lowered to improve viewing angles.
- Carts for 32 to 55 in. displays (DMCS3255SG62 and DMCS3255SG62W) have 0° to -45° tilt capability to help reduce glare.
- Carts for 37 to 70 in. displays (DMCS3770SG75 and DMCS3770SG75W) support landscape and portrait screen orientations.

SIMPLE SETUP

- VESA-compliant mounts provide no-hassle display compatibility.
- Glass shelf and base support audio/video components.

Feature focus



- A** VESA-compliant bracket accommodates most displays for simple mounting.
- B** Carts for 32 to 55 in. displays have 0° to -45° screen tilt capability. Carts for 37 to 70 in. displays can switch between portrait/landscape screen orientation.
- C** Rear bolts allow fast, secure screen height adjustment.

- D** Shelf and base conveniently support AV components; designer touches like frosted glass are both functional and attractive.
 - E** Rolling, locking casters allow convenient cart placement and relocation.
- Not Shown: Included cable covers route cables neatly along the back of the column for a polished appearance.

SPECIFICATIONS

Model	DMCS3255SG62	DMCS3255SG62W	DMCS3770SG75	DMCS3770SG75W
Supported Screen Size	32 to 55 in. (81 to 140 cm)	32 to 55 in. (81 to 140 cm)	37 to 70 in. (94 to 178 cm)	37 to 70 in. (94 to 178 cm)
Screen Orientation	Landscape	Landscape	Portrait or landscape	Portrait or landscape
Weight Capacity	130 lb. / 59 kg	130 lb. / 59 kg	175 lb. / 79 kg	175 lb. / 79 kg
Frame Construction	Metal	Metal	Metal	Metal
Shelf/Base Color, Material	Black Frosted Glass	White Frosted Glass	Black Frosted Glass	White Frosted Glass
Unit Dimensions HxWxD	61 x 31.5 x 20 in. (155 x 80 x 50 cm)	61 x 31.5 x 20 in. (155 x 80 x 50 cm)	84.6 x 31.5 x 20 in. (215 x 80 x 50 cm)	84.6 x 31.5 x 20 in. (215 x 80 x 50 cm)
Unit Height Range	50 to 61 in. (127 to 155 cm)	50 to 61 in. (127 to 155 cm)	65.7 to 84.6 in. (167 to 215 cm)	65.7 to 84.6 in. (167 to 215 cm)
Unit Weight	41.3 lb. (18.7 kg)	41.3 lb. (18.7 kg)	49.7 lb. (22.5 kg)	49.7 lb. (22.5 kg)
Supported VESA Patterns (mm)	75x75 / 100x100 / 200x100 / 200x200 / 300x300 / 400x200 / 400x300 / 400x400	75x75 / 100x100 / 200x100 / 200x200 / 300x300 / 400x200 / 400x300 / 400x400	100x100 / 200x100 / 200x200 / 300x100 / 300x200 / 300x300 / 400x100 / 400x200 / 400x300 / 400x400 / 600x400	100x100 / 200x100 / 200x200 / 300x100 / 300x200 / 300x300 / 400x100 / 400x200 / 400x300 / 400x400 / 600x400
Limited Warranty	5 Years	5 Years	5 Years	5 Years

Learn more about our full line of display mounts at tripplite.com.

TRIPP-LITE
by **EATON**