

## Smart 232 32-Port Multi-User Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22091



### Description

Multi-user access and control of many computers/servers

Straightforward set up

Space saving devices that eliminate cable clutter

From server rooms to data centers

### Features

- 32 Ports with 2 simultaneous KVM Users
- BIOS level access
- USB keyboard and mouse console
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

## Specifications

### Highlights

- 32 Ports with 2 simultaneous KVM Users
- BIOS level access
- USB keyboard and mouse console
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

### System Requirements

Operating System

- Windows, Novell, Linux, SUN Solaris

Resolution

- Supports video resolutions up to 1600 x 1200 @ 85Hz

### Package Includes

- Smart 232
- Power Cord
- RS232 Cable
- Rackmount Hardware
- Owner's Manual



Powering Business Worldwide



OVERVIEW	
UPC Code	654518209921
CONNECTIONS	
Number of Ports	32
Computer/Server Ports	32
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.50 x 13.10 x 19.80
Shipping Dimensions (hwd / cm)	13.97 x 33.27 x 50.29
Shipping Weight (lbs.)	8.10
Shipping Weight (kg)	3.67
Unit Dimensions (hwd / in.)	1.700 x 17.000 x 10.600
Unit Dimensions (hwd / cm)	4.4 x 43.1 x 27
Unit Weight (lbs.)	5.1
Unit Weight (kg)	2.31
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	2
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.