

Smart 116 SPU - 16-Port Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22182



Description

Save Space and Money

From SOHO to Enterprise

Features

- 16 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- 16 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- DOS, Windows, LINUX, UNIX, MAC and all other major operating systems

Console

- VGA Monitor
- USB or PS/2 Keyboard and Mouse

Resolution

- Supports video resolutions up to 1600 x 1200 @ 75Hz

Package Includes

- Smart 116 SPU
- USB to PS/2 Adapter
- RS232 Cable
- Power Cord
- Rackmount Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	654518212457



Powering Business Worldwide



Console	No
CONNECTIONS	
Number of Ports	16
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	6.90 x 6.80 x 11.90
Shipping Dimensions (hwd / cm)	17.53 x 17.27 x 30.23
Shipping Weight (lbs.)	4.20
Shipping Weight (kg)	1.91
Unit Dimensions (hwd / in.)	1.600 x 8.500 x 4.800
Unit Dimensions (hwd / cm)	4.15 x 21.5 x 12.2
Unit Weight (lbs.)	4.1
Unit Weight (kg)	1.86
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.