

Composite Video Gold Cable (RCA M/M), 6-ft.

MODEL NUMBER: A004-006



Description

Tripp Lite's Premium 6 ft. Composite Video Gold Cable offers superior video quality, resulting in brighter, more saturated colors, and sharper images. A Silver-Plated Copper Coaxial Center Conductor, with a low-loss dielectric, prevents signal loss and rejects video noise for the best possible picture.

Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium-grade, 99.99% Pure Copper c-Center Conductor with Silver Plating
- 6-cut, RCA connector, with split tip center pin, ensures a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- True 75 ohm impedance for widest bandwidth
- Abrasion resistant flexible PVC jacket

Specifications

OVERVIEW	
UPC Code	037332121813
Technology	Composite
CONNECTIONS	
Side A - Connector 1	RCA (MALE)
Side B - Connector 1	RCA (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black

Highlights

- High-Purity Copper Coaxial Cable for improved signal transfer and low energy loss
- Double-shielded construction for maximum EMI/RFI protection
- Silver-Plated Center Conductor for the best performance at higher video frequencies
- Excellent noise isolation with 100% aluminum/mylar foil and braid shielding

System Requirements

- Home theater equipment with RCA digital audio/video connectors

Package Includes

- 6 ft. Composite Video Gold Cable



Powering Business Worldwide



Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	0.10 x 5.00 x 9.30
Shipping Dimensions (hwd / cm)	0.25 x 12.70 x 23.62
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.