

Audio Cables (2 x RCA M/M), 6-ft.

MODEL NUMBER: A050-006



Description

Tripp Lite's premium High Resolution Gold Audio Cables are designed to provide a clear, accurate sound, as well as eliminate noise and interference that can compromise your listening pleasure. This 6 ft. cable is specifically designed for digital devices, providing better sonic accuracy and more detailed, natural sound. This cable features 75 ohm coaxial cable, made of 99.99% pure copper, and precision machined, 6-cut, Gold RCA connectors that are corrosion resistant.

Features

- Superb audio clarity with more natural sounding mid-range
- Premium-grade, 99.99% pure copper conductors
- Nitrogen-injected dielectric material delivers better high frequencies and a more realistic stereo image
- 6-cut RCA connectors, with split-tip center pin, ensure a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- Molded, color coded connectors
- Abrasion resistant flexible PVC jacket

Specifications

OVERVIEW	
UPC Code	037332121899
Technology	Stereo Audio
CONNECTIONS	
Side A - Connector 1	(2) RCA (MALE)
Side B - Connector 1	(2) RCA (MALE)
Latching or Gripping Connector	No

Highlights

- Superior audio quality for movies with Dolby Digital and DTS Surround-Sound
- High-purity copper coax for improved signal transfer and low energy loss
- Double-shielded construction for maximum EMI/RFI protection
- Silver-plated center conductor for the best high frequency response

System Requirements

- Home Theater or Stereo equipment with RCA Digital Audio connectors

Package Includes

- 6 ft. High Resolution Gold Audio Cable



Powering Business Worldwide



PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.50 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	24.13 x 17.78 x 1.27
Shipping Weight (lbs.)	0.58
Shipping Weight (kg)	0.26
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.