

230V Automatic Voltage Switch with Surge Protection, 380 Joules, Hardwired

MODEL NUMBER: AVS30D



Highlights

- 30-amp current rating
- Hardwired directly into home and office mains
- Over- and undervoltage protection
- Surge and spike protection

Package Includes

- AVS30D Automatic Voltage Switch
- Owner's manual

Description

AVS30D Automatic Voltage Switch is a complete power protection device combining overvoltage, undervoltage and spike/surge protection for your appliances and electronics. Also guards against surges and spikes that may occur when power is restored. Hardwired directly into home or office wiring, the AVS30D safeguards refrigerators, freezers, air conditioners, washers, dryers, TVs and computer equipment from fluctuating power.

Program buttons let you quickly set voltage range, on/off delay, overload protection and digital display mode. The easy-to-read digital LED displays show you voltage, wattage, settings and status at a glance. The AVS30D features surge-protecting components to guard against spikes and surges.

Features

- 30-amp current rating
- Input terminal connects to the mains power
- Output terminal connects to home or office wiring
- Program buttons
- Voltage LED
- Load LED
- Digital LED display

Specifications

OVERVIEW	
UPC Code	037332182142
INPUT	
Nominal Input Voltage(s) Supported	220V AC



Powering Business Worldwide



Recommended Electrical Service	230V
Voltage Compatibility (VAC)	230
Maximum Surge Amps	6500kA
Input Plug Type	Hard-wire
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	Hardwire
Output Amp Capacity	30
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	380
AC Suppression Response Time	<1ns
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	2.40 x 5.20 x 9.20
Shipping Dimensions (hwd / cm)	6.10 x 13.21 x 23.37
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	7.000 x 5.240 x 2.180
Unit Dimensions (hwd / cm)	17.78 x 13.31 x 5.537



Powering Business Worldwide



FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.