

## 4-Port Wall-Mountable 4K HDMI Splitter for Ultra-HD (4Kx2K) Video and Audio - 3840x2160 @ 24/30Hz

MODEL NUMBER: **B118-004-UHD-WM**



Transmit a 4Kx2K HDMI signal from a single source to four displays

### Description

Tripp Lite's B118-004-UHD-WM HDMI Splitter allows the 4K2K digital signal from a Blu-Ray player or other HDMI device to be displayed on two HDMI displays, or, connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's P566-Series cables. Installation is quick and simple, with no software or drivers to install. Locate your HDMI source up to 16.4 ft. (5 m.) from the splitter, and the splitter up to 16 ft. (5 m.) from a display, for a max distance of 23 ft. (7 m.) between splitter and display. Supports Full 3D and video resolutions up to UHD 4Kx2K 3840 x 2160 (24Hz and 30Hz). High Speed HDMI and 3D compliant, with support for 36-bit Deep Color (12-bits per channel). Supports DTS-HD, Dolby True HD, Dolby Digital Plus, and LPCM 7.1 Channel Surround Sound audio. HDCP and EDID compliant. Includes wall mounting hardware.

### Features

- Simultaneously transmit the video and audio from an HDMI source to multiple HDMI monitors
- Wall Mounting hardware included
- Supports Full 3D and video resolutions up to UHD 4Kx2K 3840 x 2160 (24Hz and 30Hz)
- Supports 36-bit Deep Color (12-bits per channel)
- Supports DTS-HD, Dolby True HD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound audio
- Supports video amplifier bandwidth of 340MHz / 3.4Gbps per channel (10.2Gbps total)
- HDCP and EDID compatible
- Plug and play; no software or drivers required
- Supports Lip Sync pass-through
- Supports xvYCC and x.vColor
- Supports the use of DVI sources and displays with the use of an optional DVI to HDMI adapter (sold separately)
- Supports a maximum distance of 16.4 ft. (5 m) from source to splitter, and 23 ft. (7 m) from splitter to display, for a total of up to 39.4 ft. (12 m)

### Highlights

- Supports Full 3D and video resolutions up to UHD 4Kx2K 3840 x 2160 (24Hz and 30Hz)
- Supports DTS-HD, Dolby True HD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound audio
- Plug and play; no software or drivers required

### Package Includes

- UHD 4Kx2K HDMI 4-port Wall Mountable Splitter
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 1.5A; Output: 5V, 3A, 4 ft.)
- Owner's Manual



Powering Business Worldwide



## Specifications

OVERVIEW	
UPC Code	037332183873
Technology	HDMI
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 5V, 3A, 4 ft.
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(4) HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.60 x 7.60 x 9.80
Shipping Dimensions (hwd / cm)	6.60 x 19.30 x 24.89
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.