

3-Port HDMI Switch for Video and Audio, 1920x1200 at 60Hz/1080p (HDMI F/3xF) with Remote Control

MODEL NUMBER: **B119-003-1**



Highlights

- Connect up to three HDMI peripherals to one HDTV
- Easily switch between devices with remote control
- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200

System Requirements

- HDMI-enabled TV or peripheral devices

Package Includes

- B119-003-1 HDMI Switch
- Remote Control
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A, 4.9 ft.)
- Owner's Manual

Description

Tripp Lite's 3-to-1 HDMI switch allows you to effortlessly switch between three HDMI video source devices such as HD satellite box, HD-DVD, Sony PS3, etc., to one HDTV. The unit supports 1.65Gbps signal rates. Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200. Switch between devices with either a pushbutton on the unit or the included remote control. Supports both audio and video digital signals as well as High-Speed HDMI v1.3 and 3D. HDCP v1.3 and EDID compatible. 1-year limited warranty.

Features

- Switch between three HDMI source devices connected to a single port on a monitor
- Switch devices via pushbutton or the included remote control
- Extend the range of the included remote control using a B119-000-REC IR receiver unit (sold separately), allowing you to locate the B119-003-1 out of sight while still being able to switch devices using the remote
- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- Supports High-Speed HDMI v1.3 and 3D
- HDCP v1.3 and EDID compatible
- Plug and play; No software or drivers required

Specifications

OVERVIEW	
UPC Code	037332181084

Technology	HDMI; IR
VIDEO	
Max Supported Video Resolution	1080p @60Hz
Max Supported Color Depth	12-bit
3D Video Supported	Yes
AUDIO	
Audio Specification	7.1 Surround Sound, Dolby True HD, DTS-HD, DSD
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
AC Power Adapter Output Specs (V / A)	5V / 1.2A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
POWER	
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	6
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	(3) HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Connector Plating	Gold
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power, Output, Input 1, Input 2, Input 3)
PHYSICAL	
Color	Black
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	2.00 x 8.00 x 6.00
Shipping Dimensions (hwd / cm)	5.08 x 20.32 x 15.24
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50



Powering Business Worldwide



Unit Dimensions (hwd / in.)	0.900 x 4.400 x 3.000
Unit Dimensions (hwd / cm)	2.4 x 11.1 x 7.5
Unit Packaging Type	Box
Unit Weight (lbs.)	0.9
Unit Weight (kg)	0.41
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	20.5 BTU/Hr
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.