

# Component Video with Stereo Audio over Cat5/Cat6 Extender, In-Line Remote Receiver, Up to 700 ft.

MODEL NUMBER: **B136-100**



### Highlights

- Remote extender unit for the B136-004 4-Port Extender/Splitter
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

### Package Includes

- B136-100 Component Video + Stereo Audio Remote Extender Unit
- Owner's Manual

### Description

The B136-100 is a remote extender unit for the B136-004 4-Port Component Video + Stereo Audio Extender/Splitter. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). Plugs directly into the TV's Component Video and Stereo Audio ports...no external power required.

### Features

- Remote extender unit for the B136-004 4-port Extender/Splitter
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- Plugs directly into the TV's Component Video and Red/White Audio ports
- No external power required

## Specifications

OVERVIEW	
UPC Code	037332155450
Product Type	Cat5/Cat6 Receiver



Powering Business Worldwide



Technology	Component; Stereo Audio
<b>VIDEO</b>	
Max 720P Range (ft)	400
Maximum Signal Range (ft)	700
Maximum Signal Range (m)	213
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	(5) RCA (MALE)
Side B - Connector 1	RJ45 (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	1.00 x 3.00 x 5.20
Shipping Dimensions (hwd / cm)	2.54 x 7.62 x 13.21
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	700
Max 480P Range (ft)	700
Max 1440 x 900 Range (ft)	400
Max 1080i Range (ft)	400
Max 480i Range (ft)	700
Max 640 x 480 Range (ft)	700
Max 800 x 600 Range (ft)	700
Max 1600 x 1200 Range (ft)	400
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.