

Component Video with Stereo Audio over Cat5 Extender Receiver Wallplate

MODEL NUMBER: **B136-100-WP**



Highlights

- Remote extender wallplate for the B136-004 4-Port Extender/Splitter
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Package Includes

- B136-100-WP Component Video + Stereo Audio Remote Extender Wallplate
- 110 Punchdown Tool
- Wallplate Mounting Screws
- Owner's Manual

Description

The B136-100-WP is a remote extender wallplate for the B136-004 4-Port Component Video + Audio Extender/Splitter. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). No external power required.

Features

- Remote extender wallplate for the B136-004 4-port Extender/Splitter
- 110 style punchdown block on back of wallplate....punchdown tool included
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Specifications

OVERVIEW	
UPC Code	037332155528
Product Type	Cat5/Cat6 Receiver
Technology	Component; Stereo Audio
CONNECTIONS	
Number of Ports	1



Powering Business Worldwide



Side A - Connector 1	(5) RCA (FEMALE)
Side B - Connector 1	110 IDC
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.10 x 4.90 x 3.00
Shipping Dimensions (hwd / cm)	2.79 x 12.45 x 7.62
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.