

Component Video with Stereo Audio over Cat5/Cat6 Extender, Wallplate Remote Receiver, Up to 700-ft.

MODEL NUMBER: **B136-100-WP-1**



Highlights

- Remote extender wallplate for the B136-004 4-Port Extender/Splitter
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable
- Eaton N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Eaton P524-01K)
- RJ45 Jack rear connection
- No external power required

Package Includes

- B136-100-WP-1 Component Video + Stereo Audio Remote Extender Wallplate
- Wallplate Mounting Screws
- Owner's Manual

Description

The B136-100-WP-1 is a remote extender wallplate for the B136-004, 4-Port Component Video + Audio Extender/Splitter. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). No external power required.

Features

- Remote extender wallplate for the B136-004 4-port Extender/Splitter
- RJ45 Jack rear connector
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Specifications

OVERVIEW	
UPC Code	037332162892
Product Type	Cat5/Cat6 Receiver
Technology	Component; Stereo Audio
VIDEO	



Powering Business Worldwide



Max 720P Range (ft)	400
Maximum Signal Range (ft)	700
Maximum Signal Range (m)	213
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	(5) RCA (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	2.50 x 3.00 x 5.00
Shipping Dimensions (hwd / cm)	6.35 x 7.62 x 12.70
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	700
Max 480P Range (ft)	700
Max 1440 x 900 Range (ft)	400
Max 1080i Range (ft)	400
Max 480i Range (ft)	700
Max 640 x 480 Range (ft)	700
Max 800 x 600 Range (ft)	700
Max 1600 x 1200 Range (ft)	400
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.