

## 21-Device AC Charging Cart for Laptops and Chromebooks - 120V, NEMA 5-15P, 10 ft. (3.05 m) Cord, Black

MODEL NUMBER: CSC21AC



Charges, secures and organizes up to 21 Chromebooks and laptops in education, healthcare, retail, warehouse and office environments.

### Features

#### Compact Mobile Charging Cart Accommodates up to 21 Chromebooks and Laptops

This 120V multi-charging station provides AC charging, secure storage and cord management for as many as 21 Chromebooks and laptops with a screen size up to 15 inches. The connected devices' AC adapters plug into 21 NEMA 5-15R outlets for charging. A built-in circuit breaker protects the devices against overloads. The laptop charging station is recommended for classrooms, businesses, medical facilities, government agencies and anywhere else that uses mobile devices on a daily basis.

#### Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure

Constructed from heavy-duty steel covered with a black powder-coated finish, this charging cart provides safe, secure storage. Devices and their power adapters are stored in separate compartments. The front and back doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

#### Moving Your Devices from Room to Room Is Easy

Large swivel casters with non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control. Corner safety bumpers protect walls and doorways from scratches. The compact Chromebook charging cart takes up about the same amount of physical space, or even less, as a typical A/V cart.

#### Well-Organized to Avoid Confusing Cable Clutter

Heavy power adapters store out of the way in removable baskets. Cables and connectors run through zoned slots and an overhead cable manager, keeping them organized and out of the way. Adjustable dividers accommodate up to seven devices per shelf, and device spaces are numbered for easy identification. A power cord wrap keeps the input cord out of the way when moving the charging station. The 10-ft. (3.05 m) cord with space-saving right-angle NEMA 5-15P plug allows great flexibility in reaching AC outlets.

#### Laminated Wood-Grain Top Doubles as a Convenient Workstation

The laminated top acts as a smooth writing surface and holds a projector, monitor or other peripherals. A pass-through RJ45 jack is provided for connecting Ethernet devices, such as a wireless router or hotspot, inside the cabinet.

## Specifications

### Highlights

- 21 internal NEMA 5-15R outlets charge mobile devices with screens up to 15 in.
- Steel enclosure locks with included keys to discourage theft, damage and tampering
- In-cabinet RJ45 jack connects Ethernet peripherals, including routers and hotspots
- Laminated wood-grain top serves as a smooth surface for writing or holding peripherals
- 10-ft. (3.05 m) cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets

### Applications

- Charge up to 21 Chromebooks and laptops in schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport connected devices from room to room with a smooth, controlled ride
- Use the laminate top as a workstation or a sturdy platform for A/V equipment

### Package Includes

- CSC21AC 21-Device AC Charging Cart, Black
- Cart handle
- Input cord wrap
- (6) Protective bumpers
- (10) Hex screws
- Hex key
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332226112
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Charger Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	21
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Frequency Compatibility	50 / 60 Hz
CHARGING	
Number of Charging Ports	21
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(21) 12A
Overcharge Protection	No
Charging Amps per Port	12A
PHYSICAL	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	46.85 x 26.77 x 29.13
Shipping Weight (kg)	68.04
Slot Dimensions - Bottom (hwd / in.)	10.11 x 1.2 x 15.58
Slot Dimensions - Bottom (hwd / mm)	256.9 x 30.48 x 395.72



Powering Business Worldwide

TRIPP LITE  
SERIES

Slot Dimensions - Middle (hwd / in.)	10.13 x 1.2 x 15.58
Slot Dimensions - Middle (hwd / mm)	257.3 x 30.48 x 395.72
Slot Dimensions - Top (hwd / in.)	10.13 x 1.2 x 15.58
Slot Dimensions - Top (hwd / mm)	257.3 x 30.48 x 395.72
Unit Dimensions (hwd / in.)	43.050 x 26.040 x 28.840
Unit Dimensions (hwd / cm)	109.35 x 66.1416 x 73.25 (con la manija instalada)
Unit Weight (lbs.)	110.23
Unit Weight (kg)	50.00
Number of Shelves	3
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); UL 1363
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.