

## Network Surge Suppressor - Essential protection for data and communication lines - BNC Coax M/F

MODEL NUMBER: D10B2



### Highlights

- Complete dataline (BNC coaxial) surge protection
- Protects against the effects of electrostatic discharge
- Lifetime product warranty
- Heavy duty grounding lead

### Description

Tripp Lite's D10B2 offers data line surge suppression for 10Base-2 (thin coax) ethernet network interface cards, bridges and routers, plus IBM 3270 and CCTV lines. Includes BNC coax male to female connections allow convenient placement at the protected device network connection. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Tripp Lite network surge suppressors reduce blown NIC cards, garbled network transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground. Six-inch heavy-gauge grounding lead connects to designated grounding lugs available on the back panel of most network workstations and pieces of internetworking equipment. Lifetime warranty.

SUPPRESSION: 1 set BNC Coax (male/female), protects center, shield & chassis, 7.5V clamping.

### Features

- D10B2 offers data line surge suppression for 10Base-2 (thin coax) ethernet connections
- Protects network interface cards, bridges and routers, plus IBM 3270 and CCTV lines
- BNC coax male to female connections connect to existing 10Base-2 wiring
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground
- 6 inch heavy gauge grounding lead connects to designated grounding lugs on protected equipment
- Lifetime product warranty

## Specifications

OVERVIEW	
UPC Code	037332010766
INPUT	
Recommended Electrical Service	120V



Powering Business Worldwide

Input Plug Type	BNC
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Output Receptacles	Hardwire
Circuit Breaker (amps)	750
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
Additional Dataline Protection	Center, Shield & Chassis
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	9.20 x 4.25 x 10.20
Shipping Dimensions (hwd / cm)	23.37 x 10.80 x 25.91
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 3.380
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>WARRANTY &amp; SUPPORT</b>	



*Powering Business Worldwide*

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.