

Dual Monitor Mount Stand for 13" to 26" Flat-Screen Displays

MODEL NUMBER: DDR1326SD



Mounts two 13–26 in. monitors on a single base to free up valuable space on your desk, table or workstation. Ideal for home or office use.

Description

The VESA-compliant DDR1326SD Dual Monitor Mount Stand mounts two monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Ideal for home and office, the DDR1326SD fits most flat-panel displays from 13 to 26 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each mount supports up to 30 pounds. The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Mounts 2 Monitors on a Base

- Frees up valuable workspace on your desk, table or workstation
- Fits most flat-panel displays from 13 to 26 in.
- Mounts adjust independently for viewing angle
- Ideal for home and office use

Convenient One-Touch Adjustment

- 180° swivel and -15° to +15° tilt capability provides comfortable viewing
- Full 360° rotation for viewing in portrait or landscape orientation

Highlights

- Fits most flat-panel displays from 13 to 26 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Each mount supports up to 30 lb.

Package Includes

- Adapter bracket assembly
- Pole
- Base
- (2) Decorative covers
- (4) M5 screws
- (4) M4 screws
- (4) D5 washers
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual



Powering Business Worldwide



Durable Metal Construction

- Each mount supports up to 30 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Mounting hardware included

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

OVERVIEW	
UPC Code	037332183477
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Maximum Weight Capacity (lbs.)	30
Maximum Weight Capacity (kg)	14
Shipping Dimensions (hwd / in.)	13.50 x 6.00 x 30.00
Shipping Dimensions (hwd / cm)	34.29 x 15.24 x 76.20
Shipping Weight (lbs.)	18.00
Shipping Weight (kg)	8.16
Unit Dimensions (hwd / in.)	14.760 x 28.030 x 11.810
Unit Dimensions (hwd / cm)	37.5 x 71.2 x 30
Unit Weight (lbs.)	11.55
Unit Weight (kg)	5.24
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.