



Powering Business Worldwide

Network Surge Suppressor - Essential protection for data and communication lines - RJ45

MODEL NUMBER: DRS232



Highlights

- Complete dataline (RS-232) surge protection
- Protects against the effects of electrostatic discharge
- Lifetime product warranty
- Heavy duty grounding lead

Package Includes

- DRS232 dataline protector
- 5-in. RJ45 patch cable
- Instruction manual with warranty information

Description

Tripp Lite's DRS232 offers dataline surge suppression for the protection of POS equipment, serial printer spoolers, multiplexers and other network devices using RS232 ports running on unshielded twisted pair (UTP). Convenient RJ45 input and output connections with included 5 inch ethernet patch cable allows convenient in-line placement at the protected device network connection. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Tripp Lite network surge suppressors reduce blown interface cards, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground. Six inch heavy gauge grounding lead connects to designated grounding lugs available on the back panel of most network workstations and pieces of internetworking equipment.

Lifetime warranty.

SUPPRESSION: 1 set RJ45 in/out jacks, protects wires 1-8, 18V clamping

Features

- DRS232 protects network devices with RS232 ports running on unshielded twisted pair lines
- Convenient RJ45 input and output connections make for simple installation (RJ45 input/output connections, pins 1-8, 18V clamping)
- 5 inch ethernet patch cable enables ideal protection placed as close as possible to the point of use
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground
- 6 inch heavy gauge grounding lead connects to designated grounding lugs on protected equipment
- Lifetime product warranty

Specifications

OVERVIEW	
UPC Code	037332010827
INPUT	
Recommended Electrical Service	120V, 230V



Powering Business Worldwide

Input Plug Type	RJ45
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	Network
Circuit Breaker (amps)	340
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
Additional Dataline Protection	1-8
Telephone/DSL Protection	No
PHYSICAL	
Housing Color	White
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
Unit Dimensions (hwd / in.)	0.890 x 1.000 x 3.570
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	



Powering Business Worldwide

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.