

Easy Pull Type-A Connectors - M/F set of VGA, 3.5mm, RCA Audio, Composite Video

MODEL NUMBER: EZA-VGACSA-2



Highlights

- SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Male to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Package Includes

- 1 x HD15/3.5mm/Red White RCA Audio/Composite Video, All Male Plugs
- 1 x HD15/3.5mm/Red White RCA Audio/Composite Video, All Female jacks + Wallplate

Description

Easy Pull Connector Kit includes: 1x HD15 Male, 1x stereo 3.5mm Plug, 2x RCA Red/White Audio plugs, and 1 x Yellow Composite Video plugs, 1 ft. pigtails. 1x HD15 Female, 1x stereo 3.5mm jack, 2x RCA Red/White Audio jacks, and 1 x Yellow Composite Video jacks, 1 ft. pigtails and wallplate. Video support up to 1600 x 1200. Use with either PVC or Plenum Easy Pull trunk cables.

Features

- Easy Pull, SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Male to Female
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. lengths, PVC or Plenum rated jackets
- Support resolutions up to 1600 x 1200

Specifications

| OVERVIEW | |
|----------------------|-----------------------------------|
| UPC Code | 037332153807 |
| Technology | Composite; Stereo Audio; VGA/SVGA |
| CONNECTIONS | |
| Side A - Connector 1 | HD15 (MALE) |
| Side A - Connector 2 | 3.5MM (MALE) |
| Side A - Connector 3 | (3) RCA (MALE) |
| Side A - Connector 4 | DIN 14 PIN (MALE) |



Powering Business Worldwide



| | |
|-------------------------------------|---------------------------|
| Side B - Connector 1 | HD15 (FEMALE) |
| Side B - Connector 2 | 3.5MM (FEMALE) |
| Side B - Connector 3 | (3) RCA (FEMALE) |
| Side B - Connector 4 | DIN 14 PIN (MALE) |
| Latching or Gripping Connector | No |
| PHYSICAL | |
| Color | Black; Green |
| Cable Length (ft.) | 1.5 |
| Cable Length (m) | 0.46 |
| Shipping Dimensions (hwd / in.) | 2.40 x 6.30 x 9.10 |
| Shipping Dimensions (hwd / cm) | 6.10 x 16.00 x 23.11 |
| Shipping Weight (lbs.) | 0.90 |
| Shipping Weight (kg) | 0.41 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.