

Protect It! 12-Outlet Home/Business Theater Surge Protector, 10-ft. Cord, 2880 Joules

MODEL NUMBER: HT1210SAT3



Highlights

- 12 outlets / 10-ft. cord
- 2880 joule rating
- 3-line 2.2GHz coaxial (gold) surge protection
- 1-line tel/modem/network (100BaseT, high-speed) surge protection

Package Includes

- HT1210SAT3 Home/Business Theater Surge Suppressor
- 6-ft. gold coax cable, 6-ft. phone cord and 6-ft. network cable
- Instruction manual with warranty information

Description

Tripp Lite's HT1210SAT3 Home/Business Theater Surge Suppressor provides advanced protection-- 2880 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 12 outlets (with transformer spacing and sliding safety covers), 3-line 2.2GHz coaxial protection and 1-line tel/modem/Ethernet (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes two diagnostic LED, 10-ft. cord with a right-angle plug, 6-ft. gold DSS cable, 6-ft. phone cord and 6-ft. network cable.

Features

- 2880 joule surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 12 widely spaced surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system while accommodating up to 4 large transformers without blocking outlets
- Sliding safety covers protect against accidental contact
- 3 sets of surge protected 2.2GHz gold coaxial connectors safeguard components on cable, satellite and antenna line; 6-ft gold DSS cable included
- 1-line tel/modem/ethernet (100BaseT, high speed) surge protection safeguards personal video recorders (PVRs) on a single dial-up or ethernet line. Built-in splitter (1 jack in and 2 jacks out) allows simultaneous connection of two devices sharing a single line; 6-ft phone and network cable included
- 10-ft cord with right angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection present (green) and grounded (red) status
- Keyhole slots provide convenient wall or cabinet mounting
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OVERVIEW	
UPC Code	037332152527
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	180000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm protection and grounding status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	330, 400, 400
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes



Powering Business Worldwide



DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 152mm; Distance between vertical tabs = 73.5mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.00 x 8.60 x 13.10
Shipping Dimensions (hwd / cm)	5.08 x 21.84 x 33.27
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	1.510 x 4.860 x 12.070
Unit Dimensions (hwd / cm)	3.84 x 12.34 x 30.66
Unit Weight (lbs.)	2.31
Unit Weight (kg)	1.05
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.