

# Power Extension Cord, C19 to Left Angle C20 - Heavy Duty, 20A, 250V, 12 AWG, 2 ft., Black

MODEL NUMBER: P036-002-20LA



Heavy-duty extension cable with left-angle C20 end allows connection of C19/C20 high-output devices in tight spaces or awkward angles.

## Features

**20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

**Left-Angle C20 Plug Makes Connecting in Tight Spaces Easier** The C19 to C20 left-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the left-angled C20 plug guides the heavy-duty extension cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

## Highlights

- Left-angle C20 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering servers, routers and other high-output network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

## Applications

- Connect devices like computers, servers and monitors to a PDU up to 2 ft. away in your data center
- Extend an existing power connection up to 2 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

## Package Includes

- P036-002-20LA C19 to Left-Angle C20 Heavy-Duty Extension Cord, 2 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332156525
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C20 - LEFT ANGLE



Powering Business Worldwide



Side B - Connector 1	IEC-320-C19
<b>PHYSICAL</b>	
Color	Black
Power Cord Jacket Type	SJT
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	0.25 x 5.20 x 8.70
Shipping Dimensions (hwd / cm)	0.64 x 13.21 x 22.10
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.