

## VGA High-Resolution RGB Coaxial Cable, Plenum Rated (HD15 M/M)), 50 ft.

MODEL NUMBER: P502-050-P



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 50 ft. apart with no ghosting.

### Description

The P502-050-P VGA Coaxial High-Resolution Plenum-Rated Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 50 feet apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. The plenum-rated jacket is ideal for running the cable through ceilings, walls and ducts.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### Features

#### Allows Connection Between VGA-Enabled Computer and Monitor Up to 50 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Plenum-rated jacket recommended for connecting through ceilings, walls and ducts

## Specifications

### OVERVIEW

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Plenum-rated jacket recommended for ceilings, walls and ducts

### System Requirements

- Display device with HD15 input
- Computer with HD15 output

### Package Includes

- P502-050-P VGA Coaxial High-Resolution Plenum-Rated Monitor Cable (M/M), 50 ft.



Powering Business Worldwide



UPC Code	037332130679
Technology	Coax; VGA/SVGA
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 1.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 2.54
Shipping Weight (lbs.)	4.10
Shipping Weight (kg)	1.86
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.