



Powering Business Worldwide

VGA Monitor Extension Cable (HD15 M/F) 15-ft.

MODEL NUMBER: P510-015



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

- Monitor with HD15 cable and resolutions up to 640x480.

Package Includes

- 15-ft. VGA Monitor Extension HD15F to HD15M Gold Connectors

Description

Tripp Lite's VGA monitor extension cable will extend the reach of a monitor cable by an additional 15-ft. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time.

For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P500-010 or P500-025.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

Specifications

OVERVIEW	
UPC Code	037332012357
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57



Powering Business Worldwide

Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.57
Shipping Weight (kg)	0.26
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.