



Powering Business Worldwide

Computer Cable, VGA Hi-Res. Replacement Cable

MODEL NUMBER: P530-006

Description

Tripp Lite's 6 foot VGA hi-resolution monitor replacement cable is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Double shielding (foil and braid) provides maximum EMI/RFI protection. HD15 male connector to 5-BNC male. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity.
- HD15 male molded connectors to 5-BNC male

Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

- Computer with HD15 female VGA port
- Monitor with 5 BNC female ports

Package Includes

- 6-ft. VGA HI-Res Monitor Cable HD15M to 5BNC Male

Specifications

OVERVIEW	
UPC Code	037332012425
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	(5) BNC (MALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 6.25 x 1.00
Shipping Dimensions (hwd / cm)	22.86 x 15.88 x 2.54
Shipping Weight (lbs.)	0.66
Shipping Weight (kg)	0.30
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.