

DVI Dual Link Cable with Audio, Digital TMDS Monitor Cable, (DVI-D and 3.5mm M/M), 10-ft.

MODEL NUMBER: P560-010-A



Description

Tripp Lite's 10 foot DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. In addition, built-in 3.5mm stereo connectors allow simultaneous connection to your computer's stereo output, to either built-in monitor speakers or external speakers. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual Link. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- 3.5MM Stereo connection molded into the assembly
- Dual Link digital signaling for transmission speeds to 9.9Gbps and 2560x1600 resolution
- Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332141019
Technology	DVI; Stereo Audio
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side A - Connector 2	3.5MM (MALE)

Highlights

- For use with Dual or Single TMDS Link specified equipment
- Molded in 3.5mm Stereo connectors
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- Monitor with DVI, and CPU with Dual Link DVI capabilities
- Stereo jack on computer, stereo jack on monitor or external speakers

Package Includes

- 10-ft. DVI Dual Link TMDS cable w/Audio - DVI-D, M/M 3.5mm, M/M



Powering Business Worldwide



Side B - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	2.00 x 7.00 x 7.00
Shipping Dimensions (hwd / cm)	5.08 x 17.78 x 17.78
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.