



Powering Business Worldwide

IEEE 1284 AA Straight Through Cable (DB25 M/M), 6-ft.

MODEL NUMBER: P710-006



Description

Tripp Lite's 6-ft. IEEE 1284 straight through cable connects a computer to a manual or automatic switchbox. It supports high-speed IEEE 1284 bi-directional communication. The cable features nickel plated DB25 male/male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems.

Features

- Connects a computer to a manual or automatic switchbox
- Supports high-speed IEEE 1284 bi-directional communication (modes: standard compatible nibble byte ECP and EPP)
- Length: 6-ft. Connectors: DB25 male/male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- 25 conductor (direct wired)
- Molded ends with easy-grip textured overmold

Specifications

OVERVIEW	
UPC Code	037332014436
Technology	Parallel
CONNECTIONS	

Highlights

- IEEE rated to support IEEE 1284 compatible auto switches
- Fully shielded against EMI/RFI interference

System Requirements

- Computer with a parallel port DB25 Female
- Parallel device or switchbox with a DB25 Female port requiring IEEE communication

Package Includes

- 6-ft. IEEE 1284 AA Straight Thru Parallel Cable DB25M to DB25M



Powering Business Worldwide

Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	DB25 (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.