



13U SmartRack 2-Post Open Frame Rack -Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST13



Description

The SR2POST13 2-Post SmartRack Open Frame Rack is an economical way to accommodate 13U of rack space for 19-inch rack-mount applications in limited spaces. Its heavy-duty, aluminum construction can safely support 800 pounds (362.9 kilograms) of rack-mount equipment. The black textured powdercoat finish makes it resistant to scratching while giving it a classic attractive appearance. The SR2POST13 is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions along with bolt-down provisions. Only standard hand tools are required for installation (9/16" wrench and 9/16" socket/ratchet). Multiple units can be bolted together side by side for easy expansion or customization as needed. The SR2POST13 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, and RoHS.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

OVERVIEW	
UPC Code	037332183644
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame

Highlights

- 13U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes

Package Includes

- SR2POST13
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual



TRIPP	LITE
	SERIES

PHYSICAL		
Color	Black	
Rack Height	13U	
Rack Depth	Extra Deep	
EIA Mounting Rails	12-24 threaded and numbered vertical mounting rails	
Maximum Device Depth (cm)	121.92	
Maximum Device Depth (in.)	48	
Maximum Device Depth (mm)	1,219	
Shipping Dimensions (hwd / in.)	4.53 x 6.50 x 30.71	
Shipping Dimensions (hwd / cm)	11.51 x 16.51 x 78.00	
Shipping Weight (lbs.)	24.00	
Shipping Weight (kg)	10.89	
Unit Dimensions (hwd / in.)	28.000 x 20.375 x 13.625	
Unit Dimensions (hwd / cm)	71.12 x 51.56 x 12.07	
Unit Weight (Ibs.)	20	
Unit Weight (kg)	9.07	
Weight Capacity - Stationary (kg)	363	
Weight Capacity - Stationary (lbs.)	800	
Number of Vertical Mounting Rails	2	
Assembly Required	Yes	
FEATURES & SPECIFICATIONS		
Pre-Installed Casters	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2025 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.