

48U SmartRack Extra-Deep Server Rack - 48 in. (1219 mm) Depth, Doors & Side Panels Included

MODEL NUMBER: SR48UBDP48



48U rack cabinet houses, organizes and secures extra-deep standard-width rack equipment in high-density server and IT networking areas.

Features

Extra-Deep Server Cabinet Accommodates 48U of Standard-Width Rack Equipment Designed for network wiring closets, retail locations, classrooms, back offices and other areas with essential rack-mount IT equipment, this SmartRack® 48U rack enclosure is 48 inches (1219 millimeters) deep. This allows high-density equipment installations, extra space for cable management, and room for removing hot-swap power supplies from the rear of mounted devices. Constructed from heavy-duty steel with a durable black powder-coated finish, the SR48UBDP48 has a maximum stationary load capacity of 3500 lbs (1588 kgs) and a maximum rolling load capacity of 2250 lbs (1020.6 kgs).

Keeps Important Equipment Secure and Easy to Access The reversible front door, split rear doors and half-size side panels lock securely to help prevent damage, tampering or theft. The doors, side panels and top panel are designed for quick release, making it easy to access connected equipment and cabling with little effort. Convenient top access ports and an open bottom allow easy cable routing through the cabinet. The vented doors allow generous airflow from front to rear to keep your equipment cool and functioning at its peak.

Easy Enclosure Deployment and Equipment Installation This 48U server rack comes fully assembled for quick and easy deployment with pre-installed casters that let you maneuver it over a level, smooth, stable surface and through a standard 7-ft. (2.13 m) doorway into position, where it can be stabilized by adjusting the levelers. Four mounting rails adjust in quarter-inch increments from four to 42 inches. Two rails also support toolless 0U mounting for quick installation of up to four compatible PDUs and vertical cable managers to help cut down on clutter.

Designed for Baying Multiple Enclosures in a Row Built-in baying brackets and removable side panels allow the combination of two or more rack cabinets in a row. Center-to-center width can be set at 24 inches (600 millimeters) to match standard data-center floor tiles.

Meets Payment Card Industry Standards The SR48UBDP48 provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

Specifications

Highlights

- 48U rack constructed from powder-coated steel that stands up to tough environments
- Mounting rails accept standard-width rack equipment up to 48 in. (1219 mm) deep
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for quick deployment on pre-installed casters
- Provides physical equipment and media security required for PCI DSS compliance

Applications

- Store and organize deeper-than-usual rack-mount equipment in a network closet, data center or other area where you need components to be secure

Package Includes

- SR48UBDP48 48U Server Rack
- (4) Side panels
- (4) Side panel locks
- (2) Keys
- (50) M6 screws
- (50) M6 washers
- (50) M6 cage nuts
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332239235
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Rack Height	48U
Rack Depth	Extra Deep
Factory Preset Rack Depth (in.)	28.125
Factory Preset Rack Depth (cm)	71.4
Factory Preset Rack Depth (mm)	714
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Minimum Device Depth (cm)	10.16
Minimum Device Depth (in.)	4
Minimum Device Depth (mm)	102
Shipping Dimensions (hwd / in.)	95.00 x 33.50 x 52.75
Shipping Weight (kg)	208.20
Unit Dimensions (hwd / in.)	89.000 x 23.630 x 50.910
Unit Dimensions (hwd / cm)	226.06 x 60.02 x 129.3114
Unit Weight (lbs.)	327.575
Unit Weight (kg)	148.59
Weight Capacity - Rolling (kg)	1,021
Weight Capacity - Rolling (lbs.)	2250
Weight Capacity - Stationary (kg)	1,588
Weight Capacity - Stationary (lbs.)	3500
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	RoHS; CE (Europe); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.