

3 Breaker Maintenance Bypass Panel for SU30K3/3, SU30K3/3XR5 and SU30K3/3INT

MODEL NUMBER: **SU30KMBPK**



Highlights

- Wallmount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy duty buswork
- Compatible with select Tripp Lite 3 phase UPS systems

Description

Wallmount 3 breaker manual bypass panel with Kirk Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 100A breaker with KAIC rating of 14/18. Key included.

Compatible with Tripp Lite SU30K3/3, SU30K3/3XR5, SU30K3/3INT

Features

- Wallmount 3 breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 100A breaker with KAIC rating of 14/18
- Key included
- Compatible with Tripp Lite SU30K3/3, SU30K3/3XR5, SU30K3/3INT

Specifications

OVERVIEW	
UPC Code	037332146267
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	240V AC; 415V AC
Voltage Compatibility (VAC)	240; 415
PHYSICAL	



Powering Business Worldwide



Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	9.75 x 24.87 x 38.20
Shipping Dimensions (hwd / cm)	24.76 x 63.17 x 97.03
Shipping Weight (lbs.)	130.00
Shipping Weight (kg)	58.97
Unit Dimensions (hwd / in.)	37.360 x 24.120 x 9.000
Unit Dimensions (hwd / cm)	94.9 x 61.3 x 22.9
Unit Weight (lbs.)	125
Unit Weight (kg)	56.70
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.