

3-Breaker Maintenance Bypass Panel for S3M80K, SV80K and SU80K

MODEL NUMBER: **SU80KMBPK**



Highlights

- Wall-mount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy-duty buswork
- Compatible with select 3-phase UPS systems

Description

Wall-mount three-breaker manual bypass panel with Kirk-Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 300A breaker with KAIC rating of 65. Key included. Compatible with S3M80K, SV80K and SU80K.

Features

- Wall-mount 3-breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 300A breaker with KAIC rating of 65
- Key included
- Compatible with S3M80K, SV80K and SU80K models

Specifications

OVERVIEW	
UPC Code	037332146298
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	240V AC
Voltage Compatibility (VAC)	240
PHYSICAL	
Form Factors Supported	Wallmount



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	62.00 x 36.87 x 12.50
Shipping Dimensions (hwd / cm)	157.48 x 93.65 x 31.75
Shipping Weight (lbs.)	375.00
Shipping Weight (kg)	170.10
Unit Dimensions (hwd / in.)	61.250 x 36.100 x 11.750
Unit Dimensions (hwd / cm)	155.6 x 91.7 x 29.8
Unit Weight (lbs.)	370
Unit Weight (kg)	167.83
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.