

40kVA 3-Phase Power Distribution Center with Integrated 3 breaker 208V Service Bypass Switch

MODEL NUMBER: **SUDC208V42P40M**



Highlights

- Full size 42U Rack Power Distribution Center supports 40kVA 3 phase UPS power distribution in datacenter equipment racks
- Integrated 3 breaker 208V service bypass switch enables hot-swap replacement of 40kVA 3 phase UPS systems without dropping the connected critical loads
- 42 pole breaker panel supports 3 phase, 208V and single phase 208V and 120V outputs to connected equipment
- Pre-installed 225A, 3 pole main breaker, ground and neutral bars
- Secure front and rear doors, removable side panels
- Full line of accessories includes circuit breakers, corded receptacle whips and PDUs

Description

Tripp Lite's SUDC208V42P40M Power Distribution Center supports 40kVA 3 phase UPS power distribution in critical datacenter equipment racks. Integrated 3 breaker 208v service bypass switch enables hot-swappable replacement of 40kVA 3 phase UPS systems without dropping the connected critical loads. Full size 42U rack enclosure with pre-installed 42 pole circuit breaker panel supports 3 phase 208V and single phase 208V and 120V outputs via optional corded receptacle whips, snap-in panel breakers and PDUs. Breaker panel includes 225A, 3 pole main breaker, ground and neutral bars, plus 1/2, 3/4 and 1 inch knockouts. Rack enclosure offers secure front and rear doors, removable side panels and shares common dimensions and overhead wiring tray accessories as Tripp Lite SR42UB rack enclosures. Compatible with Tripp Lite SUBB-series 1, 2 and 3 pole breakers, SUWL-series corded receptacle whips and a full line of compatible basic, metered, monitored and switched PDUs to support a variety of advanced network configurations.

Features

- SUDC208V42P40M Power Distribution Center supports 40kVA, 3 Phase UPS power distribution in critical datacenter equipment racks
- Integrated 3 breaker 208v service bypass switch enables hot-swappable replacement of 40kVA 3 phase UPS systems without dropping the connected critical loads
- Full size 42U rack enclosure with pre-installed 42 pole circuit panel supports 3 phase 208V and single phase 208V and 120V outputs via optional corded receptacle whips, snap-in panel breakers and PDUs
- Line up and match power distribution cabinet blends with existing standard datacenter racks for an aesthetically pleasing appearance while providing convenient connectivity between the centralized 3 phase UPS and protected electronic devices in equipment racks
- Breaker panel includes 225A 3 pole main breaker, ground and neutral bars, 1/2, 3/4 and 1 inch knockouts (see Help & Downloads for manual with detailed wiring information)
- Rack enclosure offers secure front and rear doors, removable side panels and shares common dimensions and overhead wiring tray and ladder accessories as Tripp Lite SR42UB equipment racks
- Requires appropriate SUBB-series output circuit breakers (see Related Items for list of compatible SUBB breakers)
- Optional SUWL-series cable whips and SUWEL-series extensions support a variety of connector types, voltages and cable lengths (see Related Items for list of compatible SUWL-series and SUWEL-series cabling accessories)
- Optional full line of basic, metered, monitored and switched PDUs



Powering Business Worldwide



Specifications

| OVERVIEW | |
|-------------------------------------|---|
| UPC Code | 037332160768 |
| PDU Type | Basic; Metered; Monitored; Switched; Hot-Swap |
| Accessory Type | Power Distribution Cabinet |
| Accessory Class | UPS Accessories |
| INPUT | |
| Input Phase | 3-Phase |
| PDU Plug Type | Hardwire |
| OUTPUT | |
| Output Receptacles | Hardwire |
| PHYSICAL | |
| PDU Form Factor | Vertical (0U) |
| Shipping Dimensions (hwd / in.) | 79.00 x 25.00 x 44.00 |
| Shipping Dimensions (hwd / cm) | 200.66 x 63.50 x 111.76 |
| Shipping Weight (lbs.) | 519.00 |
| Shipping Weight (kg) | 235.41 |
| Unit Dimensions (hwd / in.) | 78.500 x 23.630 x 43.000 |
| Unit Dimensions (hwd / cm) | 199.39 x 60.02 x 109.22 |
| Unit Weight (lbs.) | 496 |
| Unit Weight (kg) | 224.98 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.