

3-Breaker Parallel Tie Cabinet with Maintenance Bypass Switch (for S3M50K, S3M60K and SU60K 3-Phase UPS)

MODEL NUMBER: **SUPC2MBP60K**



Highlights

- 3-breaker parallel tie cabinet accessory for select Tripp Lite 60kVA 3-phase UPS systems
- Links the output of two UPS systems for 120kVA non-redundant operation
- Integral Maintenance Bypass switch enables UPS maintenance or replacement
- 3 built-in circuit breakers, heavy-duty copper buswork
- Compatible with Tripp Lite S3M50K, S3M60K and SU60K 3-phase UPS systems

Description

Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation. Non-redundant configuration combines the output of two UPS systems to support twice the output current. Built-in Maintenance Bypass Switch enables UPS maintenance and repair with no disruption in power to connected equipment. Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined. See owner's manual and [Tripp Lite Parallel Tie Cabinet with Bypass Panel](#) download for detailed specifications, dimensional drawings, operational flow charts and technical descriptions. Compatible with two Tripp Lite S3M50K, S3M60K and SU60K UPS systems.

Features

- Provides a means for safely paralleling two UPS systems for non-redundant combined mode operation
- Non-redundant configuration combines the output of two UPS systems to support twice the output current
- Built-in Maintenance Bypass Switch enables UPS maintenance and repair with no disruption in power to connected equipment
- Two input breakers receive incoming power from the UPS and are connected to heavy-duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined
- Compatible with two Tripp Lite S3M50K, S3M60K and SU60K UPS systems

Specifications

OVERVIEW	
UPC Code	037332167262
Accessory Type	Parallel Tie Cabinet
Accessory Class	UPS Accessories
INPUT	



Powering Business Worldwide



Nominal Input Voltage(s) Supported	208V AC
Voltage Compatibility (VAC)	208
PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	70.25 x 38.88 x 12.50
Shipping Dimensions (hwd / cm)	178.44 x 98.76 x 31.75
Shipping Weight (lbs.)	490.00
Shipping Weight (kg)	222.26
Unit Dimensions (hwd / in.)	69.500 x 38.130 x 11.800
Unit Dimensions (hwd / cm)	176.5 x 96.8 x 29.8
Unit Weight (lbs.)	485
Unit Weight (kg)	219.99
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.