



Powering Business Worldwide

208V Corded UPS Backplate Outlet Kit for SU6000RT3U, L6-30R, L6-20R, 5-15/20R

MODEL NUMBER: SUPDM12



Highlights

- Converts Tripp Lite's hardwire SU6000RT3U UPS systems to one with AC plug and outlets
- For use with 208V mains and UPS output voltage configurations
- 10 ft. / 3m AC input power cable with NEMA L6-30P input plug
- 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Description

Tripp Lite's SUPDM12 corded backplate kit converts Tripp Lite's hardwire SU6000RT3U UPS system into one with AC plug and outlets. 10 ft./3m input line cord with L6-30P plug enables simple connection to 208V 30A mains power. Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles. Easy quick-connect wiring installs in minutes.

VOLTAGE COMPATIBILITY NOTE - SUPDM12 supports SU6000RT3U applications configured for 208V nominal input voltage only (See SUPDM13 for 240V input voltage configurations).

Features

- Converts Tripp Lite's hardwire SU6000RT3U UPS system to one with an AC plug and outlets
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Specifications

OVERVIEW	
UPC Code	037332120861
Accessory Type	Backplate Outlet Kit
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	208V AC
UPS Input Cord Length (ft.)	10



Powering Business Worldwide

UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 208V
Input Connection Type	NEMA L6-30P input plug
Voltage Compatibility (VAC)	208
OUTPUT	
Output Receptacles	(10) 5-15/20R; (2) L6-20R; (1) L6-30R
Output Nominal Voltage	Simultaneous 208 and 120V output
Overload Protection	120V outlets are protected by 2 separate 20A branch rated circuit breakers
PHYSICAL	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	5.00 x 8.80 x 13.70
Shipping Dimensions (hwd / cm)	12.70 x 22.35 x 34.80
Shipping Weight (lbs.)	5.60
Shipping Weight (kg)	2.54
Unit Dimensions (hwd / in.)	2.500 x 5.000 x 11.000
Unit Dimensions (hwd / cm)	6.4 x 12.7 x 28
Unit Weight (lbs.)	6
Unit Weight (kg)	2.72
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.