

## 208/240V Single Phase Whip Extension cable in 20 ft. (6.09 m) length with L6-30R output and L6-30P input

MODEL NUMBER: **SUWEL630C-20**



### Highlights

- 208/240V single phase whip extension cable
- 20-ft. (6.09 m) length
- 3 conductor 10 AWG cable
- L6-30P plug, L6-30R outlet (208/240V 30A)

### Description

208/240V single phase whip extension cable with L6-30R outlet and L6-30P plug. 20-ft. (6.09 m) length, 10 AWG.

### Features

- 208/240V single phase whip extension cable
- L6-30R outlet and L6-30P plug
- 20-ft. (6.09 m) length
- 10 AWG

## Specifications

OVERVIEW	
UPC Code	037332156266
Accessory Type	Single-Phase Whip Cable
Accessory Class	PDU Accessories
INPUT	
Input Connection Type	L6-30P
OUTPUT	
Monitored PDU options	PDUMNV30HV (0U / 4 C19, 20 C13 outlets)
Output Receptacles	(1) L6-30R



Powering Business Worldwide



PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	20
Cable Length (m)	6.10
Shipping Dimensions (hwd / in.)	11.00 x 11.00 x 11.00
Shipping Dimensions (hwd / cm)	27.94 x 27.94 x 27.94
Shipping Weight (lbs.)	8.00
Shipping Weight (kg)	3.63
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.