

208V 3-Phase Whip in 10 ft. (3.05 m) length with L21-30R output for 3-Phase Distribution Cabinet Applications

MODEL NUMBER: **SUWL2130C-10**



Highlights

- 208V three phase whip distribution cabinet accessory
- 10-ft. (3.05 m) length with 3-ft. (0.91 m) removed outer jacket
- 5 conductor 10AWG stranded wire
- L21-30R outlet (208V 3PH 30A)

Description

208V three phase whip with L21-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 10-ft. (3.05 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB330 circuit breaker in SUDC208V series 3 phase distribution racks. L21-30R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-30P plug-in connection.

Features

- 208V three phase whip with L21-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 10-ft. (3.05 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB330 circuit breaker in SUDC208V series 3 phase distribution racks
- L21-30R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-30P plug-in connection

Specifications

OVERVIEW	
UPC Code	037332176288
Accessory Type	3-Phase Whip Cable
Accessory Class	PDU Accessories
INPUT	
Input Connection Type	Hardwire (5 wire - L1, L2, L3, N, G)
OUTPUT	



Powering Business Worldwide



PDU Recommendation Notes	Compatible with all PDU brands fitted with a L21-30P (208V 3PH 30A) input plug, including Tripp Lite PDU3MV6L2130 and PDU3VSR10L2130 and PDU3VSR3L2130
Output Receptacles	(1) L21-30R
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.00 x 12.00 x 6.00
Shipping Dimensions (hwd / cm)	30.48 x 30.48 x 15.24
Shipping Weight (lbs.)	5.80
Shipping Weight (kg)	2.63
Unit Weight (lbs.)	6.7
Unit Weight (kg)	3.04
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.