

208/240V Single Phase Whip in 10 ft. (3.05 m) length with L6-30R for Breakered 3-Phase Distribution Cabinets

MODEL NUMBER: SUWL630C-10



Highlights

- 208/240V single phase whip distribution cabinet accessory
- 10-ft. (3.05 m) length with 3-ft. (0.91 m) removed outer jacket
- 3 conductor 10AWG stranded wire
- L6-30R outlet (208/240V 30A)

Description

208/240V single phase whip with L6-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 10-ft. (3.05 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks. L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection.

Features

- 208/240V single phase whip with L6-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 10-ft. (3.05 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks
- L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection

Specifications

OVERVIEW	
UPC Code	037332156181
Accessory Type	Single-Phase Whip Cable
Accessory Class	PDU Accessories
INPUT	
Input Connection Type	Hardwire (3 wire - L, N, G)
OUTPUT	



Powering Business Worldwide



PDU Recommendation Notes	Compatible with all PDU brands fitted with a L6-30P (30A 208/240V) input plug, including Tripp Lite PDU1230 , PDUV30HV , PDUMH30HV , PDUMV30HV , PDUMNH30 , PDUMNV30, PDUMH30HV19NET , PDUMH30HVNET and PDUMV30HVNET
Output Receptacles	(1) L6-30R
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	6.40 x 11.90 x 12.00
Shipping Dimensions (hwd / cm)	16.26 x 30.23 x 30.48
Shipping Weight (lbs.)	4.80
Shipping Weight (kg)	2.18
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.