


Protect It! Surge Protector with 3 Outlets (2-fixed, 1-rotating), Direct Plug-In, 1080 Joules, Coax Protection

MODEL NUMBER: TLP31SAT



Highlights

- 3 outlet - 2 fixed outlets, 1 rotating power outlet and rotating coax
- Direct plug-in design
- 1080 joule rating
- 1-line gold coax (2.2GHz bandwidth) protection

Package Includes

- TLP31SAT Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable

Description

Tripp Lite's TLP31SAT Home/Business Theater Surge Suppressor provides high-performance protection--1080 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 3 outlets, 1-line coaxial protection safeguard an entire home/business theater system. \$25,000 Ultimate Lifetime Insurance coverage (U.S., Canada, and Puerto Rico only). Included 6 ft. gold coaxial cable.

Features

- 3 outlets - 2 fixed and 1 rotating outlet allow for easier plug connection and removal
- 1080 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 1 set of rotating surge-protected Type F gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- Diagnostic LED alerts user to protection
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into three by plugging into any wall outlet
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332180711

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Outlet Orientation	Rotatable
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
UL1449 Let Through Rating	400, 500, 500
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
Telephone/DSL Protection	No



Powering Business Worldwide



PHYSICAL	
Color	Black
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.51 x 3.35 x 2.56
Shipping Dimensions (hwd / cm)	14.00 x 8.51 x 6.50
Shipping Weight (lbs.)	0.79
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	5.110 x 3.150 x 1.380
Unit Dimensions (hwd / cm)	12.98 x 8 x 3.5
FEATURES & SPECIFICATIONS	
Rotatable Outlets	Yes
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.