

Protect It! Surge Protector with 4 Side-Mounted Outlets , Direct Plug-In, 720 Joules

MODEL NUMBER: TLP4BK



Highlights

- 4 side-mounted outlets (including 2 transformer-friendly outlets)
- Direct plug-in design
- 720 joule rating
- Diagnostic LEDs

Package Includes

- TLP4BK Surge Suppressor
- Instruction manual with warranty information

Description

The TLP4BK Surge Suppressor has four side-mounted outlets (including two transformer-friendly outlets), a convenient direct plug-in design and diagnostic LEDs. The unit has a surge suppression rating of 720 joules to handle the strongest surges.

Features

- 4 side-mounted outlets allows easier plug connection and removal (including 2 transformer-friendly outlets)
- Direct plug-in design converts two outlets into four by plugging in to any wall outlet
- Surge suppression rating: 720 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate protection present & ground present
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332138392
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120



Powering Business Worldwide

TRIPP LITE
SERIES

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Side-mounted
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	720
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	6.70 x 1.50 x 2.80
Shipping Dimensions (hwd / cm)	17.02 x 3.81 x 7.11
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	5.000 x 2.200 x 1.600
Unit Dimensions (hwd / cm)	12.7 x 5.59 x 4.06
Unit Weight (lbs.)	0.36
Unit Weight (kg)	0.16
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.