


Protect It! 6-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Ethernet Protection, Safety Covers

MODEL NUMBER: TLP66NET



Highlights

- 6 outlets / 6-ft cord
- 1080 joule rating
- Ethernet surge protection

Package Includes

- TLP66NET
- 6-ft. network cable
- Instruction manual with warranty information

Description

Tripp Lite's TLP66NET surge suppressor has 6 outlets, a 6-ft. cord and diagnostic LEDs. The unit has a surge suppression rating of 1080 joules to handle the strongest surges. Built-in RJ45 jacks prevent surges from damaging your network equipment (6-ft network cable included). \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets with integrated child safety covers
- 6ft cord
- Built-in RJ45 jacks prevent surges from damaging your network equipment (6ft. network cable included)
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- Can accommodate up to 2 transformers without blocking remaining outlets
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Lighted power switch
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332159700 |
| INPUT | |



Powering Business Worldwide



| | |
|--|---|
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 72000 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 1.83 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (6) 5-15R |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A resettable illuminated combo switch / circuit breaker |
| Transformer Accommodation | (4) Yes |
| Outlet Orientation | Block style with two rows of 3 outlets |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Switches | Combination AC circuit breaker and 2-position red illuminated on/off power switch |
| Diagnostic LED Details | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1080 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| UL1449 Let Through Rating | 400v |
| EMI / RFI Filtering | Up to 40 dB |
| Automatic Shut-Off | Yes |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | Yes |



Powering Business Worldwide



| | |
|--|---|
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Color | Light Gray |
| Material of Construction | Plastic |
| Power Cord Color | Light Gray |
| Mounting Holes or Slots | Yes |
| Slot or Hole Mount Measurement (Center to Center) | 119mm |
| Outlets Measurement (Center to Center) | Distance between standard outlets = 28.5; Distance between standard outlet and transformer outlet = 48.5mm |
| Receptacle Color | Gray |
| Shipping Dimensions (hwd / in.) | 11.10 x 2.00 x 7.20 |
| Shipping Dimensions (hwd / cm) | 28.19 x 5.08 x 18.29 |
| Shipping Weight (lbs.) | 1.90 |
| Shipping Weight (kg) | 0.86 |
| Unit Dimensions (hwd / in.) | 1.500 x 4.230 x 8.290 |
| Unit Dimensions (hwd / cm) | 3.81 x 10.74 x 21.06 |
| Unit Weight (lbs.) | 1.32 |
| Unit Weight (kg) | 0.60 |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$25,000 Ultimate Lifetime Insurance |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.